

**EPG 45****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

**General ordering data**

Type	EPG 45
Order No.	<a href="#">1500830000</a>
Version	Pressing tool, 6mm <sup>2</sup> , 150mm <sup>2</sup>
GTIN (EAN)	4050118309317
Qty.	1 pc(s).

## EPG 45

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Technical data

## Dimensions and weights

Width	370 mm	Width (inches)	14.567 inch
Height	123 mm	Height (inches)	4.843 inch
Depth	80 mm	Depth (inches)	3.15 inch
Weight	2,500 g	Net weight	500 g

## Environmental Product Compliance

REACH SVHC Lead 7439-92-1

## Technical data

Charging time 0.5 h

## Description of contact

Crimping range, min. 6 mm<sup>2</sup> Crimping range, max. 150 mm<sup>2</sup>

## tool data crimping

Drive	Electro-hydraulic	Wire end ferrules cross-section, min.	6 mm <sup>2</sup>
Wire end ferrules cross-section, max.	150 mm <sup>2</sup>	Deviation	16 mm

## Classifications

ETIM 3.0	EC001282	ETIM 4.0	EC001282
ETIM 5.0	EC000168	ETIM 6.0	EC000168
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

## Approvals

ROHS Conform

## Downloads

Brochure/Catalogue [CAT 3 HDC 17/18 EN](#)  
[CAT 6 TOOLS 15/16 EN](#)

**Data sheet**

**EPG 45**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

