

**Pressing tool
CTI 6 G ZERT**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Crimping tools for insulated connectors**

cable lugs, terminal pins, parallel and serial connectors,
plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

General ordering data

Type	CTI 6 G ZERT
Order No.	1292880000
Version	Pressing tool, Tool for insulated cable connectors, 0.5mm ² , 6mm ² , Oval crimp, Parallel crimp
GTIN (EAN)	4050118089165
Qty.	1 pc(s).

Data sheet

**Pressing tool
CTI 6 G ZERT**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	250 mm	Width (inches)	9.842 inch
Weight	747 g	Net weight	750 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Description of contact

Type of contact	Insulated connector	Crimping range, min.	0.5 mm ²
Crimping range, max.	6 mm ²		

tool data crimping

Crimping profile 1, min.	0.5 mm ²	Crimping type/profile	Oval crimp, Parallel crimp
Crimping profile 1, max.	1.5 mm ²	Crimping profile 2, min.	1.1 mm ²
Crimping profile 2, max.	2.5 mm ²	Crimping profile 3, min.	2.6 mm ²
Crimping profile 3, max.	6 mm ²		

Classifications

ETIM 3.0	EC001282	ETIM 4.0	EC001282
ETIM 5.0	EC000168	ETIM 6.0	EC000168
UNSPSC	23-17-16-04	eClass 5.1	21-04-91-14
eClass 6.2	21-04-38-11	eClass 7.1	21-04-38-11
eClass 8.1	21-04-38-11	eClass 9.0	21-04-38-11
eClass 9.1	21-04-38-11		

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
--------------------	--------------------------------------

Data sheet

**Pressing tool
CTI 6 G ZERT**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

