

SlimFix X
SFX 11/60 MC NE WS V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



SlimFix X are halogen-free conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. SlimFix is an acknowledged and approved marker type in traffic engineering. The SF tool allows easy installation even in case of small markers.

- Halogen-free material
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	SFX 11/60 MC NE WS V0
Order No.	1432750000
Version	SlimFix X, Conductor and cable markers, 7 - 40 mm, 60 x 11 mm, white
GTIN (EAN)	4050118237382
Qty.	60 pc(s).
compatible printer	1324380000

SlimFix X SFX 11/60 MC NE WS V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	11 mm	Width (inches)	0.433 inch
Height	60 mm	Height (inches)	2.362 inch
Depth	0.8 mm	Depth (inches)	0.031 inch
Net weight	2.117 g		

General data

Colour	white	Halogen	No
Material	Polyamide 66	Material colour according to resistance code	9
Operating temperature range	-40...100 °C	Recommended industries	Transportation, Machinery
Size of labelling field	44 x 11 mm	UL 94 flammability rating	V-0
Version	Installation with cable ties	Width	11 mm

Conductor and cable markers

Conductor O.D.	7 - 40 mm	Conductor O.D., max.	40 mm
Conductor O.D., min.	7 mm	Conductor cross-section, max.	500 mm ²
Conductor cross-section, min.	16 mm ²	Halogen	No

Classifications

ETIM 3.0	EC001288	ETIM 5.0	EC001288
ETIM 6.0	EC001530	eClass 6.2	27-40-04-01
eClass 7.1	27-14-91-29	eClass 8.1	27-14-91-03
eClass 9.0	27-40-04-01	eClass 9.1	27-40-04-01

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP

SlimFix X
SFX 11/60 MC NE WS V0

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings