

HS-FR 1.2-2.4/25 MM W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**MultiMark**

With MultiMark you have a fast and reliable marking system at your disposal to enable virtually any kind of marking. Connectors, conductors, cables or devices – the MultiMark product family offers a well-structured, practical range of markers which can be used in combination with our advanced M-Print® PRO configuration software for all areas of use.

Your benefits with MultiMark

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

General ordering data

Type	HS-FR 1.2-2.4/25 MM W
Order No.	2621560000
Version	Conductor and cable markers, 1.2 - 2.4 mm, 24.9 x 4 mm, white
GTIN (EAN)	4050118625486
Qty.	2,000 pc(s).
compatible printer	2430920000

HS-FR 1.2-2.4/25 MM W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Width	4 mm	Width (inches)	0.157 inch
Height	24.9 mm	Height (inches)	0.98 inch
Depth	0.77 mm	Depth (inches)	0.03 inch
Net weight	0.2 g		

General data

Colour	white	Halogen	No
Material	Polyolefine	Operating temperature range	-55... 125 °C
Size of labelling field	4 x 24.9 mm	Width	4 mm

Conductor and cable markers

Conductor O.D.	1.2 - 2.4 mm	Conductor O.D., max.	2.4 mm
Conductor O.D., min.	1.2 mm	Conductor cross-section, max.	0.5 mm ²
Conductor cross-section, min.	0.25 mm ²	Halogen	No
Rate of shrinkage	2:1	Recommended shrinking temperature	90 °C
Wire connection cross section AWG, max.	AWG 20	Wire connection cross section AWG, min.	AWG 24

Classifications

ETIM 5.0	EC001530	ETIM 6.0	EC001530
eClass 6.2	27-40-04-01	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

HS-FR 1.2-2.4/25 MM W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

