

THM
THM WO 15/70 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Type	THM WO 15/70 WS
Order No.	1429440000
Version	THM, Conductor and cable markers, 9.6 - 12.7 mm, 15 x 70 mm, white
GTIN (EAN)	4050118233872
Qty.	1 pc(s).
compatible printer	2430920000 2448870000

THM

THM WO 15/70 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	70 mm	Width (inches)	2.756 inch
Height	15 mm	Height (inches)	0.591 inch
Depth	0.025 mm	Depth (inches)	0.001 inch
Net weight	112 g		

General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Halogen	No
Material	Polyester film	Number per roll	500
Operating temperature range	-40...150 °C	Size of labelling field	30 x 15 mm
Type of printing	neutral	UL 94 flammability rating	V-0
Version	Self-adhesive	Width	70 mm

Conductor and cable markers

Conductor O.D.	9.6 - 12.7 mm	Conductor O.D., max.	12.7 mm
Conductor O.D., min.	9.6 mm	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	0.75 mm ²	Halogen	No

Classifications

ETIM 5.0	EC001530	ETIM 6.0	EC001530
eClass 6.2	27-40-04-01	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-29	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
Software	M-Print PRO configuration file

THM THM WO 15/70 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

