

**SwitchMark
SM DIA 60-22 K MC NE GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



With an outer diameter of 60 mm, the SwitchMark SM DIA 60-22 offers plenty of room to label markers for emergency stop with 22 mm holes. The adhesive film on the back ensures a secure hold.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Please note that these markers are not intended for printing with the SpeedMarking laser.

General ordering data

Type	SM DIA 60-22 K MC NE GE
Order No.	1323750000
Version	SwitchMark, Device markers, 60 x 60 mm, ø 60 - 22 mm, Siemens 3 SB, Eaton Moeller M22-PV, yellow
GTIN (EAN)	4050118127010
Qty.	10 pc(s).
compatible printer	1324380000

SwitchMark SM DIA 60-22 K MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	60 mm	Width (inches)	2.362 inch
Height	60 mm	Height (inches)	2.362 inch
Depth	1.2 mm	Depth (inches)	0.047 inch
Net weight	10.3 g	Diameter	22 mm

General data

Application/manufacture	ø 60 - 22 mm, Siemens 3 SB, Eaton Moeller M22-PV	Colour	yellow
Halogen	No	Material	Polyamide 66
Operating temperature range	-40...100 °C	UL 94 flammability rating	V-2
Version	Self-adhesive	Width	60 mm

Device markers

Diameter	22 mm
----------	-------

Classifications

ETIM 5.0	EC001288	ETIM 6.0	EC001288
eClass 6.2	27-37-12-25	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
Software	M-Print PRO configuration file

SwitchMark SM DIA 60-22 K MC NE GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

