



### Tamper evident security labelling, thermal transfer

#### Helatag 1203 (Silver)

Electrical and electronic identification. Security and warranty identification of components, housings and nameplates.


#### Features and Benefits

- Tamper-evident labels leave clear reminder that label has been removed
- Mark assets securely and unambiguously
- Print labels with customer unique references
- Use text, graphics and barcodes as required
- Excellent print performance using TT822OUT ribbon
- Print with TT4000+, TT430 for best results
- Easy label design with Tagprint Pro



Highly visible tamper evidence.

<b>MATERIAL</b>	Type 1203, Polyester (PET), silver matt (SR), tamper-proof
<b>Operating Temperature</b>	-40 °C to +120 °C
<b>Curing Temperature</b>	from +7 °C
<b>Adhesive</b>	Acrylic
<b>Thickness of Foil (µm)</b>	53 µm
<b>Chem. Material Properties</b>	Excellent resistance to water, alcohol, most oils, greases, fuel, freezing fluid, brake fluid, aliphatic solvents, weak acids, salts and alkalis.
<b>Recommended Ribbon Type</b>	TT822OUT
<b>Specifications</b>	CSA, UL-Recognised



TYPE	Width (W)	Height (H)	Width of Liner (WL)	Labels per Row	Pack Cont.	Colour	Article-No.
TAG71TD6-1203-SR	12.7	11.1	101.6	6	15,000 pcs.	Silver (SR)	596-71120
TAG15TD3-1203-SR	25.4	12.7	85.1	3	7,500 pcs.	Silver (SR)	596-51203
TAG27TD2-1203-SR	38.1	19.1	85.1	2	2,500 pcs.	Silver (SR)	596-71203
TAG67TD2-1203-SR	38.1	31.8	85.1	2	1,000 pcs.	Silver (SR)	596-67120
TAG73TD1-1203-SR	50.8	25.4	55.0	1	2,000 pcs.	Silver (SR)	596-73120
TAG66TD1-1203-SR	50.8	36.5	56.8	1	1,000 pcs.	Silver (SR)	596-66120
TAG68TD1-1203-SR	63.5	25.4	69.0	1	2,000 pcs.	Silver (SR)	596-68120
TAG63TD1-1203-SR	63.5	38.1	70.0	1	1,000 pcs.	Silver (SR)	596-63120
TAG76TD1-1203-SR	63.5	50.8	70.0	1	500 pcs.	Silver (SR)	596-76120
TAG62TD1-1203-SR	76.2	50.8	82.0	1	500 pcs.	Silver (SR)	596-21203
TAG64TD1-1203-SR	88.9	36.5	95.0	1	1,000 pcs.	Silver (SR)	596-64120
TAG98TD1-1203-SR	101.0	160.0	105.0	1	250 pcs.	Silver (SR)	596-98120
TAG97TD1-1203-SR	101.6	74.0	106.0	1	500 pcs.	Silver (SR)	596-97120

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



For product specific approvals and specifications please refer to the Appendix.