THM ET 28/28 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The Weidmüller range of conductor and cable marker products provides users with solutions for a wide variety of applications. The field of application ranges from thin conductors to cables with large outside diameters. The product range includes combination systems with individual tags, transparent sleeves and markers which can be fastened with cable ties.

Open and closed markers, as well as printed or blank markers for individual labelling are available. Weidmüller's halogen-free and low-emission conductor markers are in compliance with European standards as well as with the in-house standards of well-known plant manufacturers.

Markers for conductors and cables - Systems are available for:

- Clipping on pre-printed markers to suit individual labelling requirements
- Labelling with characters from a standard character set
- Combining individual, pre-printed characters to form a character code
- Customer labelling with SMark laser, PrintJet, MCP Plus plotter, MC-Mobilo, laser printer (DIN A4 format), thermal transfer printer or STI pen

A selection of samples can be found in the Weidmüller conductor marker sample bag, order No. 1640420000.

General ordering data

Type	THM ET 28/28 WS
Order No.	2539410000
Version	Conductor and cable markers, 28 x 28 mm, white
GTIN (EAN)	4050118570182
Qty.	1,500 pc(s).

THM ET 28/28 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	28 mm	Width (inches)	1.102 inch
Height	28 mm	Height (inches)	1.102 inch
Depth	0.35 mm	Depth (inches)	0.014 inch
Net weight	0.387 g		

General data

Colour	white	Halogen	No
Material	Polypropylene	Operating temperature range	-50…100 °C
UL 94 flammability rating	HB	Width	28 mm

Conductor and cable markers

Halogen	No

Classifications

ETIM 6.0	EC001288	eClass 6.2	27-40-04-01
eClass 9.0	27-40-06-29	eClass 9.1	27-40-06-29

Approvals

ROHS	Conform

Downloads

Engineering Data	EPLAN

THM ET 28/28 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

