

## ESG

### ESG-F 9/20 MC NE WS

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from the following manufacturers:

- Siemens
- Télémecanique
- ABB
- Beckhoff
- Lumberg
- Tags for all-purpose usage; self-adhesive or clip-on tags, depending on the type

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

Please note that these markers are not intended for printing with the SpeedMarking laser.

#### General ordering data

Type	ESG-F 9/20 MC NE WS
Order No.	<a href="#">2556510000</a>
Version	ESG, Device markers x 20 mm, Colour: white
GTIN (EAN)	4050118568943
Qty.	200 pc(s).
compatible printer	<a href="#">1324380000</a>

Creation date May 27, 2019 8:13:31 PM CEST

## Data sheet

**ESG**  
**ESG-F 9/20 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technical data

### Dimensions and weights

Width	20 mm	Width (inches)	0.787 inch
Height	9 mm	Height (inches)	0.354 inch
Net weight	0.41 g		

### General data

Application/manufacture	Festo / CPV 18	Colour	white
Halogen	No	Printed characters	neutral
UL 94 flammability rating	V-2	Width	20 mm

### Classifications

ETIM 6.0	EC001288	eClass 6.2	27-14-91-29
eClass 9.0	27-40-06-29	eClass 9.1	27-40-06-29

### Approvals

ROHS	Conform
------	---------

**Data sheet**

**ESG**  
**ESG-F 9/20 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

