

CP P2
Single-point load cell made of aluminium

Technical data

- Accuracy in accordance with OIML R60 C3
- RoHS compliant
- Protection against dust and water splashes IP65 (in accordance with EN 60529)
- Aluminium alloy, anodized
- Suitable for price computing scales, bench scales etc.
- Maximum platform size
  100 – 300 kg: 400×400 mm
  400 – 500 kg: 450×450 mm
- 4-wire connection
- Nominal sensitivity: 2 mV/V
- Cable length: 2 m
- Version in accordance with OIML R60 C4 or C5 on request

STANDARD: IP 65, 1 DAY
OPTION: DAkkS, ISO

Model	Nominal load
SAUTER	kg
CP 100-3P2	100
CP 150-3P2	150
CP 200-3P2	200
CP 300-3P2	300
CP 400-3P2	400
CP 500-3P2	500




CP P7
Single-Point load cell made of stainless steel

Technical data

- Accuracy in accordance with OIML R60 C3
- RoHS compliant
- Protection against dust and water splashes IP67 (in accordance with EN 60529)
- Stainless steel
- Area of application: Mass as well as compressive force measurement in harsh environmental conditions
- Suitable for price computing scales, bench scales etc.
- Maximum platform size: 400×400 mm
- 6-wire connection
- Nominal sensitivity: 2 mV/V
- Cable length: 1 m
- Version in accordance with OIML R60 C4 on request

STANDARD: IP 67, 1 DAY
OPTION: DAkkS, ISO

Model	Nominal load
SAUTER	kg
CP 30-3P7	30
CP 50-3P7	50
CP 75-3P7	75
CP 100-3P7	100
CP 150-3P7	150



CP P8
Single-point load cell made of aluminium

Technical data

- Accuracy in accordance with OIML R60 C3
- RoHS compliant
- Protection against dust and water splashes IP65 (in accordance with EN 60529)
- Aluminium alloy, anodized
- Suitable for price computing scales, bench scales etc.
- Maximum platform size: 600×600 mm
- 6-wire connection
- Nominal sensitivity: 2 mV/V
- Cable length: 3 m
- Version in accordance with OIML R60 C4 or C5 on request

Discover more details and matching accessories online!

STANDARD: IP 65, 1 DAY
OPTION: DAkkS, ISO

Model	Nominal load
SAUTER	kg
CP 50-3P8	50
CP 100-3P8	100
CP 150-3P8	150
CP 200-3P8	200
CP 250-3P8	250
CP 300-3P8	300
CP 500-3P8	500
CP 600-3P8	600