

# JOY-VIEW 15

Portable 15.6" USB-C Display with Touchscreen



Whether web content or games, notebook, smartphone or game console, the Joy-View is a display for every occasion.

The Joy-View was developed for the USB-Type-C interface and has, in addition to its Full-HD resolution, a high-quality touchscreen. Many other devices, such as game consoles, are supported via an additional mini HDMI port.

The enclosed Smart Case protects the Joy-View not only during every transport. The case's adjusting function also ensures a safe, upright stand. So with the Joy-View you are prepared for every application.

## KEY FEATURES

Dimensions	360 x 230 x 10mm
Items delivered	Joy-View 15 Display, Smart Case, 1.5m HDMI to miniHDMI Cable, 1m TypeC to TypeC Cable, 1m USB-A to USB-C Cable, Power Adapter, HDMI to mini HDMI Adapter, Cleaning Towel

## DISPLAY SPECIFICATIONS

Resolution	1920 x 1080
Screen Size	15.6"
Refresh Rate	60Hz
Contrast	800:1
Brightness	300nit
Screen Type	TFT IPS LCD
Backlight	LED Backlight
Color Gamut	16.7M, NTSC 72%, sRGB up to 100%
Speaker	Double Speaker 8Ω2W
Viewing Angle	178°
Aspect Ratio	16:9
Power Supply	5-20V or Type-C USB 3.0
Inputs	Mini HDMI, Type-C, Voltage Input
Outputs	3.5mm Jack Plug



## SUPPORTED USB-C DEVICES

Gaming Consoles

Nintendo Switch Tablet

Huawei

Mate 10, Mate 10 Pro, Mate 20 Pro, Mate 20 X, Mate 20, Mate 20 RS, P20 Pro, P20, P30, P30 Pro, MateBook 13, MateBook X Pro, MateBook X, MateBook E

Samsung

Galaxy S8, Galaxy S8+, Galaxy S9, Galaxy S10, Galaxy Tab S4, Galaxy Tab A, Galaxy Book2, Galaxy Tab S3, Galaxy Book, Notebook 9 Pro, Notebook 7 Spin, Notebook 9, Notebook Flash

Apple

iPad Pro (2018), MacBook, MacBook Pro, MacBook Air, iMac, iMac Pro

Microsoft

Surface Book 2

Asus

VivoBook Flip, ROG STRIX Hero Edition, ROG Zephyrus M GM501GS, ROG STRIX Scar Edition, ZenBook Pro 15, ZenBook S, ROG STRIX, ROG STRIX GL503VD-UH73

Dell

XPS9380, XPS 13 9370, Inspiron 13, Inspiron 15, Alienware 17, Alienware 15 R4, Latitude 5590, G3 17, Inspiron 7777

HP

Pavilion x360, ENVY x360, Pavilion 15-CC610MS, ENVY x2, Pavillion 15-CX0051MS, ENVY x2 Detachable 12-E068MS, ENVY Notebook 17-U193MS, Pavilion Gaming Desktop 790-0021, Pavilion 24-XA0031

Lenovo

Legion Y7000, Miix 630,  
Flex 14 81EM000LUS,  
Flex 14 81EM000KUS,  
Flex 5 81CA0013US,  
Ideapad 720S, Flex 5  
81CA0016US, Ideacentre  
730S

#### ADDITIONAL INFORMATION

Operating Temperature	0 - 50°C
Case	Aluminum Alloy
Article No.	JT-View15
EAN	4250236818894
Customs Tariff No.	8473302000