


Copper cable lugs

PKD-series

PKD-series cable lugs are compatible with compressed copper wires. Inner and outer dimensions are smaller in size compared to PK-series.



| STK code | Product code | Product name | Conductor (mm ²) | D (mm) | L (mm) | L1 (mm) | d1 (mm) | d2 (mm) | b (mm) | Package (pce) |
|-----------|--------------|--------------|------------------------------|--------|--------|---------|---------|---------|--------|---------------|
| 52 012 02 | VA02-0006 | PKD 10-5 | 10 | 5,5 | 29 | 23,0 | 4,5 | 7,0 | 11 | 100 |
| 52 012 04 | VA02-0007 | PKD 10-6 | 10 | 6,5 | 30 | 23,0 | 4,5 | 7,0 | 11 | 100 |
| 52 012 06 | VA02-0008 | PKD 10-8 | 10 | 8,5 | 32 | 24,0 | 4,5 | 7,0 | 13 | 100 |
| 52 012 10 | VA02-0009 | PKD 16-6 | 16 | 6,5 | 33,5 | 26,5 | 5,5 | 8,5 | 13 | 100 |
| 52 012 12 | VA02-0010 | PKD 16-8 | 16 | 8,5 | 35,5 | 27,5 | 5,5 | 8,5 | 15 | 100 |
| 52 003 74 | VA02-0011 | PKD 16-10 | 16 | 10,5 | 38,5 | 29,5 | 5,5 | 8,5 | 16 | 100 |
| 52 003 32 | VA02-0012 | PKD 16-12 | 16 | 12,5 | 42,5 | 31,5 | 5,5 | 8,5 | 18 | 100 |
| 52 012 14 | VA02-0013 | PKD 25-6 | 25 | 6,5 | 37 | 30,0 | 7,0 | 10,0 | 14 | 100 |
| 52 012 16 | VA02-0014 | PKD 25-8 | 25 | 8,5 | 38 | 30,0 | 7,0 | 10,0 | 15 | 100 |
| 52 012 18 | VA02-0015 | PKD 25-10 | 25 | 10,5 | 42 | 32,0 | 7,0 | 10,0 | 16 | 100 |
| 52 003 33 | VA02-0016 | PKD 25-12 | 25 | 12,5 | 46 | 35,0 | 7,0 | 10,0 | 18 | 100 |
| 52 012 20 | VA02-0017 | PKD 35-6 | 35 | 6,5 | 41 | 33,0 | 8,5 | 12,0 | 17 | 100 |
| 52 012 22 | VA02-0018 | PKD 35-8 | 35 | 8,5 | 42,5 | 33,5 | 8,5 | 12,0 | 17 | 100 |
| 52 012 24 | VA02-0019 | PKD 35-10 | 35 | 10,5 | 44 | 34,0 | 8,5 | 12,0 | 17 | 100 |
| 52 003 34 | VA02-0020 | PKD 35-12 | 35 | 12,5 | 47,5 | 36,5 | 8,5 | 12,0 | 19 | 100 |
| 52 012 26 | VA02-0021 | PKD 50-8 | 50 | 8,5 | 47,5 | 38,5 | 10,0 | 14,0 | 21 | 100 |
| 52 012 26 | VA02-0022 | PKD 50-10 | 50 | 10,5 | 49 | 39,0 | 10,0 | 14,0 | 21 | 100 |
| 52 012 30 | VA02-0023 | PKD 50-12 | 50 | 12,5 | 52 | 42,5 | 10,0 | 14,0 | 23 | 100 |
| 52 012 32 | VA02-0024 | PKD 70-8 | 70 | 8,5 | 52 | 43,0 | 12,0 | 16,5 | 24 | 50 |
| 52 012 34 | VA02-0025 | PKD 70-10 | 70 | 10,5 | 53 | 43,0 | 12,0 | 16,5 | 24 | 50 |
| 52 012 36 | VA02-0026 | PKD 70-12 | 70 | 12,5 | 56 | 44,0 | 12,0 | 16,5 | 24 | 50 |
| 52 012 38 | VA02-0005 | PKD 95-8 | 95 | 8,5 | 60 | 48,0 | 13,5 | 18,0 | 27 | 50 |
| 52 012 40 | VA02-0001 | PKD 95-10 | 95 | 10,5 | 60 | 48,0 | 13,5 | 18,0 | 27 | 50 |
| 52 012 42 | VA02-0027 | PKD 95-12 | 95 | 12,5 | 60 | 48,0 | 13,5 | 18,0 | 27 | 50 |
| 52 004 53 | VA02-0003 | PKD 120-10 | 120 | 10,5 | 69 | 55 | 15 | 19,5 | 28 | 25 |
| 52 004 54 | VA02-0028 | PKD 120-12 | 120 | 12,5 | 69 | 55 | 15 | 19,5 | 28 | 25 |
| 52 004 56 | VA02-0029 | PKD 120-14 | 120 | 14 | 69 | 55 | 15 | 19,5 | 28 | 25 |
| 52 004 57 | VA02-0030 | PKD 150-10 | 150 | 10,5 | 76 | 60 | 16,5 | 21 | 32 | 25 |
| 52 004 58 | VA02-0031 | PKD 150-12 | 150 | 12,5 | 76 | 60 | 16,5 | 21 | 32 | 25 |
| 52 004 59 | VA02-0032 | PKD 150-14 | 150 | 14 | 76 | 60 | 16,5 | 21 | 32 | 25 |

Customer-specific cable lugs and connectors

We also produce cable lugs and connectors with special requirements. If you can't find connector that satisfies you, we design one for your purpose!!

