

## Product information

# 00 21 42

## Tool Case "BIG Twin" Electric

63 parts



- Equipped with 14 KNIPEX tools, a total of 63 brand tools, partly VDE-tested according to DIN EN 60900
- With a total of 95 inserting options
- Max. payload: 25 kg
- Volume: 38 litres
- Free-standing in all opening positions thanks to snap-in cover holders with hinge mechanism on both sides, angle freely adjustable
- Can be opened from one or both sides; bottom and lid can be opened independently of each other
- Label field with two stickers for individual labelling
- Heavy duty ABS material, black
- Circumferential aluminium frame with securely mounted, sturdy centre wall that can be fitted on both sides, with versatile inserting options due to elasticated loops and twelve small pockets
- Metal hinges
- Three-digit combination lock for secure locking of the case
- Two metal tilt locks each for fixing the cover and the base
- Removable document compartment and removable tool board made from dirt-repelling twin-wall PP sheets with 13 tool pockets
- Base tray, can be fixed by press button, height 58 mm, can be subdivided by flexible inserts; cover plate with six large compartments



### General

|                 |                    |
|-----------------|--------------------|
| Article No.     | 00 21 42           |
| EAN             | 4003773084228      |
| Weight          | 11,550 g           |
| Dimensions      | 290 x 435 x 265 mm |
| REACH compliant | contains SVHC      |
| RoHS compliant  | not applicable     |

### Technical details

|                                         |                 |
|-----------------------------------------|-----------------|
| Dimension exterior (interior) width mm  | 520 mm (490 mm) |
| Dimension exterior (interior) height mm | 435 mm (370 mm) |
| Dimension exterior (interior) depth mm  | 290 mm (110 mm) |

### Content

|              |                                                                                                                                                                                                                                               |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 08 26 145    | 1 x Needle-Nose Combination Pliers (145 mm)<br>⚡ 1000 V                 |
| 12 52 195 SB | 1 x KNIPEX PreciStrip16® Automatic Insulation Stripper (0,08 - 16 mm²)                                                                                                                                                                        |
| 13 86 200    | 1 x Pliers for Electrical Installation (Ø 15 mm / 50 mm²)<br>⚡ 1000 V   |
| 16 95 01 SB  | 1 x KNIPEX ErgoStrip® Universal Stripping Tool for right-handers (Ø 8,0 – 13,0 mm)<br>                                                                     |
| 86 03 180    | 1 x Pliers Wrench pliers and a wrench in a single tool (180 mm)<br>                                                                                        |
| 97 53 04     | 1 x Self-Adjusting Crimping Pliers for wire ferrules with lateral access (0,08 – 10 + 16 mm²)                                                                                                                                                 |

| Content     |                                                                                                                                                                                                                                                                                                                                             |
|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|             | MM                                                                                                                                                                                                                                                         |
| 98 20 35 SL | 1 x Screwdriver (Slim) for slotted screws (0,6 x 3,5 x 100 mm)<br>⚡ 1000V                                                                                                                                                                                  |
| 98 25 01 SL | 1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ1 x 80 mm)<br>⚡ 1000V                                                                                                                                                                        |
| 98 52       | 1 x Cable Knife (190 mm)<br>⚡ 1000V                                                                                                                                                                                                                                                                                                         |
| 00 11 01    | 1 x Knipex KNIPEX TwinKey® Control Cabinet Key for all standard cabinets and shut-off systems (92 mm)                                                                                                                                                                                                                                       |
| 26 26 200   | 1 x Knipex Snipe Nose Side Cutting Pliers (Stork Beak Pliers) (200 mm)<br>⚡ 1000V   40°  |
| 70 06 160   | 1 x Knipex Diagonal Cutter (160 mm)<br>⚡ 1000V                                                                                                                                                                                                             |
| 74 06 200   | 1 x Knipex High Leverage Diagonal Cutter (200 mm)<br>⚡ 1000V                                                                                                                                                                                               |
| 87 01 180   | 1 x Knipex KNIPEX Cobra® High-Tech Water Pump Pliers (180 mm)<br>                                                                                                                                                                                          |
| 101-0300    | 1 x Picard Locksmith's hammer (300 g)                                                                                                                                                                                                                                                                                                       |
| 361 252 1   | 1 x Rennsteig Electrician's Chisel (250 x 10 mm)                                                                                                                                                                                                                                                                                            |
| 16135       | 1 x Stabila Spirit Level Type 70 Electric (430 mm)                                                                                                                                                                                                                                                                                          |
| 18115       | 1 x Stabila Pocket Electric mini spirit level (68 mm)                                                                                                                                                                                                                                                                                       |
| 003760      | 1 x Wera Joker open-end wrench (10 x 13 mm)                                                                                                                                                                                                                                                                                                 |
| 004018      | 1 x Wera 8100 SA 8 Zyklus set of metal ratchets 28 parts (1/4")                                                                                                                                                                                                                                                                             |
| 5003484001  | 1 x Wera VDE interchangeable blades, 16 parts, slim                                                                                                                                                                                                                                                                                         |
| Accessories |                                                                                                                                                                                                                                                                                                                                             |
| 00 21 42 LE | Tool Case "BIG Twin" empty,                                                                                                                                                                                                                                                                                                                 |

technical change and errors excepted