

R45603172

Socket set
1/2"-3/8"-1/4"
172 pieces



- > For hand-operated screw work
- > Plastic case in GEDORE red Design

Code	No.	Contents	Pieces	Weight
3300058	R45603172	1/4" 2K lever reversible ratchet, fine-toothed, 72 teeth 150 mm 1/4" square plug-in handle 165 mm 1/4" socket wrench insert, hexagon SW 4 4.5 5 5.5 6 7 8 9 10 11 12 13 14 25 mm 1/4" socket wrench insert hexagon SW 4 5 6 7 8 9 10 50 mm 1/4" socket wrench insert TX E4 E5 E6 E7 E8 25 mm 1/4" screwdriver bit socket hexagon socket 3 4 5 6 37 mm 1/4" screwdriver bit socket slotted 4 5.5 6.5 7 37 mm 1/4" screwdriver bit socket cross-slotted PH 0 1 2 37 mm 1/4" screwdriver bit socket cross recess PZ 0 1 2 37 mm 1/4" screwdriver bit socket TX T8 T9 T10 T15 T20 T25 T27 T30 37 mm 1/4" screwdriver bit socket TX with bore T8 T9 T10 T15 T20 T25 T27 T30 37 mm 1/4" socket wrench extension 50 100 mm 1/4" T-handle with slider 115 mm 1/4" universal joint 32 mm bit adapter 1/4" square x 1/4" hex. 25 mm 1/4" bits TX T5 T6 T7 25 mm 1/4" bits TX with hole T7 25 mm 1/4" bits TX plus security T10 T15 T20 T25 T27 T30 T40 T45 25 mm 1/4" bits multi-tooth XZN M5 M6 M8 25 mm 1/4" bits keyway M5 M6 M7 M8 M9 25 mm 5/16" bits hexagon socket 7 8 10 12 14 30 mm 5/16" bits slotted 8 10 12 30 mm 5/16" bits cross recess PH 3 4 30 mm 5/16" bits cross recess PZ 3 4 30 mm 5/16" bits TX T40 T45 T50 T55 T60 T70 30 mm 5/16" bits TX with bore T40 T45 T50 T55 T60 T70 30 mm 3/8" 2K lever reversible ratchet, fine-toothed, 72 teeth 180 mm 3/8" socket wrench insert hexagon SW 10 11 12 13 14 15 16 17 18 19 3/8" socket wrench insert hexagon SW 10 11 12 13 14 15 63 mm 3/8" socket wrench insert TX E10 E11 E12 E14 E16 E18 3/8" spark plug insert SW 18 mm 65 mm 3/8" socket wrench extension 150 mm 3/8" universal joint 49 mm bit adapter 3/8" square x 5/16" hex 30 mm 1/2" 2K lever reversible ratchet, fine-toothed, 72 teeth 250 mm 1/2" socket wrench insert hexagon SW 10 11 12 13 14 15 16 17 18 19 20 21 22 24 27 30 32 1/2" socket wrench insert 6-kant SW 16 17 18 19 22 77 mm 1/2" socket wrench insert TX E20 E24 1/2" spark plug insert SW 16 21 mm 65 mm 1/2" socket wrench extension 125 250 mm 1/2" universal joint 66 mm enlarging piece / sliding piece 3/8" x 1/2" 44 mm bit adapter 1/2" square x 5/16" hex 38 mm offset screwdriver set hexagon SW 1.5 2 2.5 3 4 5 6 mm	172	10,5