


HDMI™ 2.0 Hybrid Active Optical Cable

HDR 4K 60Hz M/M 50m/ 164,04ft



4K 60Hz



Product Name

HDMI™ 2.0 Hybrid Active Optical Cable
HDR 4K 60Hz M/M 50m/ 164,04ft

Product Series

Cables

Itemcode

CAC-1391

EAN code

8719214471088

UPC code

841615101276

Description:

The Club 3D HDMI™ 2.0 Hybrid Active Optical Cable features both copper and fiber conductors, providing a lighter, more flexible cable construction, which makes it ideal for installation in narrow spaces and over longer distances. The perfect solution for conference rooms, classrooms, digital signage displays, and more.

This CAC-1391 features a built-in booster circuit that is self-powered through the HDMI ports, allowing you to connect your HDMI-enabled devices at a distance of up to 50 meters with no signal loss.

The cable is Halogen Free, and produced according to the International Electrochemical Commission's Restriction Use of Halogen (IEC 61249-2-21) directive. This cable features unidirectional architecture, which requires that the cable is installed in the correct direction. Please refer to the "source" and "display" labels on the HDMI connectors, in order to ensure that the cable is connected properly.

Features:

- Compliant to HDMI™ specification version 2.0b (600Mhz Clock Frequency)
- Gold plated connectors for maximum conductivity
- Supports UHD TV resolutions up to 4096x2160p @ 60Hz
- Supports 3D resolutions up to 1080p Full HD @ 120Hz
- Total Data bandwidth of 18Gbps
- Supports Dolby® True HD, DTS-HD Master Audio up to 32 audio channels
- Halogen Free and without EMI/RFI emission
- Support for HDR/HDCP/EDID/CEC/DDC
- Plug and Play, no driver software required
- Unidirectional - meaning Source and Display only
- This cable is Hybrid which makes it downwards compatible to other HDMI versions

OS Support:

All

In the box:

- HDMI™ 2.0 Hybrid Active Optical Cable HDR 4K 60Hz M/M 50m/ 164,04ft

Input:

- HDMI™ 2.0 Male

Output:

- HDMI™ 2.0 Male

Other info:

- Box size: 230 x 230 x 100 mm.
- Box Weight: 162 gr.
- Product Weight: 1348 gr.
- Cable + Bag : 1357 gr.
- Product + Box + Bag Weight: 1519 gr.
- Product height: 100 mm.
- Product width: 190 mm.
- Product Length: 50 meter/ 164,04 feet
- Meets ROHS, FCC, and CE EMI requirements
- Made in China

Input:



Output:



senseVISION
w e connect

Disclaimer:
While we endeavor to provide the most accurate, up-to-date information available, the content on this document may be out of date or include omissions, inaccuracies or other errors. Therefore Club 3D does not accept any rights claimed on the content of this document. Please refer to a full overview of our Legacy Terms and Conditions on www.club-3d.com. All other brand names are trademarks or registered trademarks and are the property of their respective owners. All content is subject to change without prior notice.