

Product information

00 21 11

Tool Bag "Compact"

Electric

14 parts



- Equipped with 12 KNIPEX tools, a total of 12 brand tools, partly VDE-tested according to DIN EN 60900
- With a total of 15 inserting options
- Compact tool case for the service technician
- Suitable as an insert for: "Basic" 00 21 05 LE, "BIG Basic Move" 00 21 06 LE, "BIG Twin Move" 00 21 41 LE, "BIG Twin" 00 21 42 LE, "BIG Twin Move RED" 98 99 15 LE and other popular tool cases
- With 8 tool pouches and 7 tool straps
- Slip-through back strap to attach to a trolley
- Made from tough polyester fabric, with zip fastener
- Dimensions exterior (W x H x D): 410 x 60 x 290 mm

General

Article No.	00 21 11
EAN	4003773084532
Weight	2,975 g
Dimensions	290 x 296 x 61 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details

Dimension exterior (interior) width mm	410 mm
Dimension exterior (interior) height mm	60 mm
Dimension exterior (interior) depth mm	290 mm

Content

12 40 200	1 x Self-Adjusting Insulation Stripper (0,03 – 10,0 mm ²) MM
13 86 200	1 x Pliers for Electrical Installation (Ø 15 mm / 50 mm ²) △ 1000V  
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool for right-handers (Ø 8,0 – 13,0 mm) MM
78 06 125	1 x Electronic Super Knips® VDE (125 mm) △ 1000V MM 
97 53 04	1 x Self-Adjusting Crimping Pliers for wire ferrules with lateral access (0,08 – 10 + 16 mm ²) MM 
98 20 35 SL	1 x Screwdriver (Slim) for slotted screws (0,6 x 3,5 x 100 mm)

Content	
	⚠ 1000V 
98 24 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH2 x 100 mm) ⚠ 1000V 
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ1 x 80 mm) ⚠ 1000V 
98 25 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ2 x 100 mm) ⚠ 1000V 
98 52	1 x Cable Knife (190 mm) ⚠ 1000V
70 06 160	1 x Knipex Diagonal Cutter (160 mm) ⚠ 1000V 
87 01 250	1 x Knipex KNIPEX Cobra® High-Tech Water Pump Pliers (250 mm) 
Accessories	
00 21 11 LE	Tool Bag "Compact" empty,

technical change and errors excepted