

Part No	90NB0MI1-M02420
Model Name	S532FA-BN134T
EAN Code	4718017472241
UPC Code	192876472248
LCD Cover Color & Decoration	GREEN-METAL
Top Case Color & Decoration	GREEN-METAL
On board processor	Intel® Core™ i5-10210U Processor 1.6 GHz (6M Cache, up to 4.2 GHz)
Operating System	Windows 10 (64bit)
Office	Includes 1 month Trial for New Microsoft Office 365 Customers
Display	15.6'//Narrow border//300nits//FHD 1920x1080 16:9//Anti-Glare//NTSC: 72%//Wide View
Number Pad	N/A
ScreenPad™	ScreenPad™
Chipset	N/A
Memory Slot	1x
Total System Memory	4GB on board + DRAM DDR4 4GB
On board memory	4GB on board
Memory Max.	12G
DIMM Memory	DRAM DDR4 4GB
Storage	PCIEG3x2 NVME 512GB M.2 SSD
Expansion Slot(includes used)	DDR4*1 M.2 2280 PCIE G3X2 *1 M.2 2280 SATA3 *1
EMMC/ISSD	N/A
External video display modes	HDMI 1.4
Discrete/Share	Share
IGPU	Intel® UHD Graphics
Video memory	N/A
Video Camera	HD IR/RGB Combo Camera
FingerPrint	N/A
On board Wireless	N/A
Wireless(Module)	Wi-Fi 6(Gig+)(802.11ax)+Bluetooth 5.0 (Dual band) 2*2
LAN	N/A
Card Reader	Type: Micro SD
USB Port	2x USB 2.0 1x USB3.1 Type A (Gen1) 1x USB3.1 Type C (Gen 1)
Interface	1x Headphone-out & Audio-in Combo Jack 1x HDMI

Audio	Built-in array microphone Audio by ICEpower® harmon/ kardon
Weight (Kg)	1.60 KG (Without Battery) 1.80 KG (with 3 cell battery)
Dimension (cm)	35.7(W) x 23.0(D) x 1.80 ~ 1.80 (H) cm
AC Adapter	ø4.0 45W AC Adapter Output: 19V DC, 2.37A, 45W , Input: 100~240V AC 50/60Hz universal
Battery	42WHrs, 3S1P, 3-cell Li-ion
Replaceable Battery	No
Keyboard type	Illuminated Chiclet Keyboard
Software	ASUS Live Update ASUS GiftBox ASUS Splendid McAfee Internet Security(Trial version)
Security	BIOS Booting User Password Protection
Supplied Accessories	
Warranty	2 years Carry-In Germany and Austria

