

SAUTER CO 200-Y1

Miniature cylindrical load cell made from stainless steel

KERN

Load cell - Combined error	0,5%
Temperature coefficient - characteristic value	$\pm 0.05\%$ F.S. / $10\text{ }^{\circ}\text{C}$
Zero balance	$\pm 1 \sim 1.5\text{mV/V}$
Temperature coefficient - zero signal	$\pm 0.05\%$ F.S. / $10\text{ }^{\circ}\text{C}$
Creep error (30 minutes)	$\pm 0.05\%$ FS
Safe overload	150%
Ultimate overload	200%

Functions

IP protection - complete device	IP65
---------------------------------	------

Construction

Material	steel, stainless
Design	Load cell
Dimension ($\varnothing \times H$)	20×12 mm
Cable length	2 m
Mounting - force application	Thrust piece (from customer side)
Mounting - force dissipation	3 × threaded hole M3

Environmental conditions

Use temperature [Min]	0 $^{\circ}\text{C}$
Use temperature [Max]	40 $^{\circ}\text{C}$

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration (compressive force)	963-262V
--	----------

Product information

GTIN/EAN number	4045761233003
REACH classification	no prohibited substances

Packing & Shipping

Shipping method	Parcel service
Delivery time	1 d
Dimensions packaging (W×D×H)	120×90×85 mm
Net weight approx.	0,05 kg
Gross weight approx.	0,10 kg
Shipping weight	0,2 kg

Category	
Brand	Sauter
Product category	Measuring cell
Product group	Load/force measuring cell
Product family	CO Y1

Measuring System	
Weighing capacity [Max]	200 kg
Measuring range force [Max] (N)	2 kN
Load cell - characteristic value - nominal	1,5 mV/V
Load cell OIML class	G5
Load cell connection	4-wire
Power supply + Colour	red
Power supply - Colour	black
Signal + Colour	green
Signal - Colour	white
Measuring applications	force mass
Directions of force	compression
Load cell - Input resistance - nominal	350 Ω
Load cell - Input resistance - variance	20 Ω
Load cell - Output resistance - nominal	350 Ω
Load cell - Output resistance - variance	3 Ω
Load cell - Recommended excitation voltage [Min]	9 V
Load cell - Recommended excitation voltage [Max]	12 V
Load cell - Isolation resistance - [Min]	5000 M Ω

SAUTER CO 200-Y1



Miniature cylindrical load cell made from stainless steel

Pictograms

STANDARD



OPTION

