



Part No	90NB0P71-M00850
Model Name	UX481FA-BM020T
EAN Code	4718017462938
UPC Code	192876462935
LCD Cover Color & Decoration	1A-Celestial Blue Eccentric circle hair-line, Metal
Top Case Color & Decoration	1A-Celestial Blue magnesium-aluminum
On board processor	Intel® Core™ i7-10510U Processor 1.8 GHz (8M Cache, up to 4.9 GHz)
Operating System	Windows 10 (64bit)
Office	Includes 1 month Trial for New Microsoft Office 365 Customers
Display	14.0'//Narrow border//300nits//FHD 1920x1080 16:9//Anti-Glare//NTSC: 72%//Wide View
Number Pad	N/A
ScreenPad™	ScreenPad™ Plus
Chipset	N/A
Memory Slot	N/A
Total System Memory	16GB on board
On board memory	16GB on board
Memory Max.	16G
How to upgrade memory	Not Available
Storage	PCIeG3x2 NVME 512GB M.2 SSD
Expansion Slot(includes used)	M.2 2280 PCIe G3X4 *1
EMMC/ISSD	N/A
External video display modes	HDMI 1.4
Discrete/Share	Share
IGPU	Intel UHD Graphics 620
Video memory	N/A
Video Camera	HD IR Camera
FingerPrint	N/A
On board Wireless	802.11ax+Bluetooth 5.0 (Dual band) 2*2
LAN	N/A
Card Reader	Type: Micro SD
USB Port	1x USB3.1 Type A (Gen1) 1x USB3.1 Type A (Gen2) 1x USB3.1 Type C (Gen 2)
Interface	1x Headphone-out & Audio-in Combo Jack 1x HDMI 1.4

Audio	Built-in speaker Built-in microphone Built-in array microphone Sonic Master harmon/ kardon
Weight (Kg)	1.40 KG (Without Battery) 1.50 KG (with 4 cell battery)
Dimension (cm)	32.3(W) x 22.3(D) x 1.99 ~ 1.99 (H) cm
AC Adapter	ø4.5 65W AC Adapter Output: 19V DC. 3.42A. 65W . Input : 100~240V AC. 50/60Hz universal
Battery	70WHrs, 4S1P, 4-cell Li-ion
Replaceable Battery	No
Keyboard type	Illuminated Chiclet Keyboard
Keyboard Specification	N/A
Software	ASUS FaceID ASUS Live Update ASUS GiftBox ASUS Solendid
Security	TPM (Firmware TPM)
Supplied Accessories	Sleeve, Stylus
Warranty	2 years Carry-In Germany and Austria

