

DATA SHEET

Creation Date: 12. Aug 2020 12:22
Page 1

MÜLLER LICHT

MÜLLER-LICHT International GmbH
Goebelstraße 61/63 – 28865 Lillienthal – Tel./Phone: +49-4298-93700 – Fax: +49-4298-9370555

Our registered trademarks:

MÜLLER
LICHT 

Technical details

Item-No. **404040**
Item Group: **LED/Outdoor-Wegeleuchten/Strom**
Description **tint LED Garden Lights Petunia, 3 pcs, white+color**



Technology

Product data

Length [mm] **60**
Width [mm] **60**

Height [mm] **350**
Weight [g] **2190.00**
Outside usage **yes**

CE **yes**
Brand **Müller-Licht**

Electrical data

Voltage nominal [V] **220-240**
Voltage measured [V] **230**
Power nominal [W] **14.00**
Power measured [W] **14.00**

Power max. [W] **9.14**
Lifetime nominal [h] **50000**
Frequency nominal [Hz] **50**
Power type **AC**
Current nominal [mA] **160**

Electric power factor [-] **0.38**
Dimability **no**
Switch cycles before failure **100000**
Weighted power consum. [kWh/1000h] **14**

Lighting data

Luminous flux nominal [lm] **750**
Luminous flux rated [lm] **750**
Luminous flux maximal [lm] **750**
Candela nominal [cd] **79**
Candela measured [cd] **79**

Rated light efficiency nominal [lm/W] **54**
Kelvin [K] **2700**
Light color **tint white+color**
(1800-6500K+RGB)
Color rendering index Ra [>=] **80**

Std. deviation of color matching initial [SDCM] [<] **6**

Environmental data

Information

Luminaire data

3x Gartenleuchte IP44
3x Erdspieß
List of components
of Netzteil (Primär 230-240 V/50 Hz, Sekundär 21 V DC), IP44
Anschlussleitung IP44, 9 m
Bedienungsanleitung
Ca-ble ending
CEE 7/17 unearthed plug

Ca-ble sleeve
Rubber black
Ca-ble length [mm] **3000**
Pro-tection class **III**

Driver

IP **44**
Owner name **Xing Yuan Electronics**

Type **XY18Z-2100710H-EO**
main power plug adapter AC->AC/
DC(<=250W)

Packing

Colorbox

Weight [g] **330.00**
pcs. **1**

Qty. of cont. products **3**
Barcode1 **4018412672865**
Code type 1 **EAN/UCC-13**

CE **yes**
WEEE **yes**

Blister

Weight [g] **0.00**

Inner box

Weight [g] **0.00**

Tray

Weight [g] **0.00**

Shrink

Weight [g] **0.00**

Transport carton

Weight [g] **560.00**
pcs. **2**

Barcode1 **4018412672957**
Code type 1 **EAN/UCC-13**
Barcode2 **0194018412672950300002**

Code type 2 **EAN128**

Manual

Notice

List of components **3x tint Garden lights**
3x Ground spikes
Distribution wire
Plug-in power pack
Operating instructions

DATA SHEET

Creation Date: 12. Aug 2020 12:22
Page 2

MÜLLER LICHT

MÜLLER-LICHT International GmbH
Goebelstraße 61/63 – 28865 Lilienthal – Tel/Phone: +49-4298-93700 – Fax: +49-4298-9370555

Our registered trademarks:
MÜLLER
LICHT **Starlicht**

Technical details

Item-No. **404040**
Item Group: **LED/Outdoor-Wegeleuchten/Strom**
Description **tint LED Garden Lights Petunia, 3 pcs, white+color**



Spectrum

