

Gigaset outdoor camera

Always keep an eye on your property with the weatherproof (IP66) outdoor camera from Gigaset.

Highlights:

- Live view in Full HD / Record* in HD Quality (*cloud package required)
- Weatherproof (IP66)
- Infrared night vision up to 15m
- Viewing angles of 110° horizontally and 60° vertically
- Encrypted real-time video transmission
- Notifications via push message or email
- Wireless connection via WiFi or via Ethernet
- Peer-to-Peer data transmission in same network
- Sound Recordings
- Different available recording packs for intrusion / motion



User examples

The outdoor camera helps the police

In the past only 17% of all burglaries in Germany were resolved. In those cases the Gigaset outdoor camera can provide you with valuable evidence. The camera buffers automatically 3 seconds of the livestream and in case of an alarm saves the recording permanently. This recording can later help the police. Thanks to HD-quality details and faces are very sharp and crystal clear. Even in dark surroundings everything is perfectly visible due to infrared.

Burglars are always in view thanks to the outdoor camera

If an alarm is triggered on your smartphone, don't panic. You want to be sure that your children have not just forgotten to switch off the alarm after school, before you call the police or your neighbors. A glance into the Gigaset elements app is all you need - you know what is happening and can act immediately in case of emergency.

Storm damage? The Gigaset outdoor camera lets you know

You are on vacation or out and about and a violent thunderstorm rages at home? With the Gigaset outdoor camera you can check any time if everything is safe and dry at home. In case of emergency you can react quickly and inform your neighbors in order to avoid costly damages.

Free Gigaset elements app:



Apple, das Apple Logo und iPhone sind Marken der Apple Inc., die in den USA und weiteren Ländern eingetragen sind. App Store ist eine Dienstleistungsmarke der Apple Inc. Google, Android, Google Play und andere Marken sind Marken der Google Inc.

Technical specifications

Gigaset outdoor camera:

- Dimensions: 190 x 60 x 60mm
- Weight: 465g
- Video resolution: Live view in Full HD (1920 x 1080p) / Record in HD Quality (1280 x 720p)
- Protection class: IP66 (weatherproof/waterproof)
- Night vision: Infrared night vision up to 15m
- Viewing angles: 110° horizontally and 60° vertically
- Connectivity: WiFi 802.11 b/g/n 2.4 GHz & Ethernet LAN
- Security standards: WPA2/ TKIP

Requirements:

- WiFi or Ethernet near outdoor camera
- Power socket indoor near outdoor camera
- A 16mm hole in the facade (for the connecting cable)
- The free Gigaset elements app
- Current iOS or Android version

Packaging includes:

- 1x Gigaset outdoor camera
- 1x WiFi antenna
- 1x Power supply unit (indoor)
- 1x Connection box (Ethernet + Power)
- 1x Drilling set
- 1x Quick Start Guide

Gigaset

Wherever you go.