



Fast-Wireless Charging Pad - 10 W

Qi™-Certified, 10 W, 7.5 W and 5 W Charging; Round Charging Base; Black

Part No.: [102186](#)

EAN-13: 0766623102186 | UPC: 766623102186

Simple, Fast Phone Charging with the Manhattan Wireless Charging Pad

Charging your phone is even simpler with the Manhattan Wireless Charging Pad - 10 W. Whether your phone has wireless charging built-in or your phone case supports wireless charging, a quality wireless charger from Manhattan makes it easy to get power back into your phone fast. With a dedicated charging pad, there's no need to find the right cable or worry about slower charging from a low-amp wall charger every time your phone needs power. Once you set it on the charger, your phone gets the fastest charge it can handle — from 10 W, 7.5 W or 5 W. Plus, as long as it isn't made of metal and is less than 5 mm (0.2 in.) thick, your phone case won't interfere with charging, so it stays protected even while it's on the pad. The Manhattan Wireless Charging Pad - 10 W truly offers a no-hassle way to charge up your phone fast.

Features:

- Qi™-certified to ensure a safe charge for you and your devices
- Up to 10 W fast-charging of compatible smartphones and wireless-charging phone cases
- Built-in safety technology that shuts off power output when metal is detected to prevent interference or device damage
- LED indicators for easy status monitoring
- Overload, overcurrent and overheating protection
- Effective wireless charging through phone cases up to 5 mm thick*
- Compact, portable and stylish design for easy travel
- *External metallic accessories (such as credit cards, magnets, grips, and phone cases) will interfere with the charging technology
- Three-year warranty

Specifications:

Standards and Certifications

- Qi™
- CE
- RoHS
- FCC
- WEEE

General

- USB-C input: DC 5 V / 2 A – 9 V / 2 A
- Wireless power output:
 - Input at 5 V / 2 A: 5 W
 - Input at 9 V / 2 A: up to 10 W
- Wattage settings (maximum):
 - 5 W / 7.5 W / 10 W
- Charging distance: ? 10 mm
- Charging efficiency: ? 80%

Protection Characteristics

- Short circuit (SCP) with auto-recovery mode
- Overvoltage (OVP) with auto-recovery mode
- Overcurrent (OCP) — current limit: 150% (max)
- Over-temperature (OTP)

Physical

- Dimensions: 90 x 90 x 10.6 mm (3.54 x 3.54 x 0.42 in.)
- Weight: 0.059 kg (2.08 oz.)
- Housing: ABS + PC

Operating Environment

- Operation Temperature: 0 – 30°C (32 – 86°F)
- Storage Temperature: -20 – 65°C (-4 – 149°F)
- Humidity (noncondensing): 10 – 90%

Compatibility

- 10 W Fast Charge Mode:
 - Samsung Galaxy S7 / S7 Edge / S8 / S8+ / S9 / S9+ / S10 or above
 - Samsung Note 8 / 9 / 10 or above
- 7.5 W Mode:
 - Apple iPhone 8 / 8 Plus / X / XR / XS / XS Max or above
- 5 W mode:
 - All other Qi™-enabled devices

System requirements

- Up to 10 W output:

- Quick Charge 2.0 / 3.0 charger
- Power Delivery 18 W charger
- 5 W:
- 5 V / 2 A charger

Package Contents

- Wireless Charging Pad - 10 W
- 1.5 m (5 ft.) USB-C power cable
- Quick Instruction Guide



