

RL73K3AR39JTDF

✓ ACTIVE

CGS | CGS RL73

TE Internal #: 2-1622825-1

CGS RL73, Surface Mount Resistors, Current Sensing Resistor, 2 Termination, 2512, Taped & Reeled, 5 %, Thick Film, Resistance Class Up to 1kΩ, .39 Ω

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors > Thick Film Resistor: Current Sense



Resistor Type: **Current Sensing Resistor**
Number of Terminations: **2**
Package Size Code: **2512**
Packaging Method: **Taped & Reeled**
Passive Component Tolerance: **5 %**

[All Thick Film Resistor: Current Sense \(796\)](#)

Features

Product Type Features

Product Type	Fixed Resistor
Resistor Type	Current Sensing Resistor
Package Size Code	2512
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Passive Component Tolerance	5 %
Resistance Class	Up to 1kΩ
Resistance Value	.39 Ω
Power Rating	1 W

Termination Features

Number of Terminations	2
Surface Mount Resistor Termination Type	Solder

Dimensions

Passive Component Dimensions	6.35 x 3.1 x .6 mm
------------------------------	--------------------



Usage Conditions

Temperature Coefficient	±200 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-C339-R529
Thick Film Resistor: Current Sense

TE Part # CAT-C339-R529B
Thick Film Resistor: Current Sense



Also in the Series | CGS RL73

Surface Mount Resistors(855)

Customers Also Bought

TE Part #1-1622825-4
Thick Film Resistor: Current Sense

TE Part #1-1623782-5
Wirewound Resistor: Vertical Mount

TE Part #826949-5
5P MOD2 STIFT LEI

TE Part #1-1705951-1
Modular Jack SE, 8/8, Gold flash

TE Part #1-1337485-0
SMC Str PCB Skt 50Ohm Gold Plt

TE Part #1-1879133-4
RN 0603 1K13 0.1% 10PPM 1K RL

TE Part #1-1705949-1
RJ22 Connectors

TE Part #1-1768812-3
LBC-11017

Documents

Product Drawings

RL73K 3A R39 5% 1K RL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1622825-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1622825-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1622825-1_BA.3d_stp.zip



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
1309350_PASSIVE_COMPONENT

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English

SMD Low Ohmic Current Sense Resistors - Type RL73 Series

English

Product Environmental Compliance
Product Compliance

English

Product Compliance

English