

# LogiLink®



## 48W Dual USB-C™ GaN Wall Charger

Art. No.: PA0231

High Efficiency 48W dual USB-C wall charger with GaN technology to charge your smartphones, tablets and laptops at full speed; compact size to carry anywhere.



### Built-in GaN Technology

By replacing the silicon wafer with gallium nitride (GaN) that takes performance to new heights with faster speeds and greater efficiency.



### Advanced Dual USB-C Power Delivery

48W dual outputs for a variety of PD devices from laptops to smart phones, powers your devices at unprecedented speeds.

Best Connectivity



RoHS compliant



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.



PA0231



4 052792 057751

Made in China

# LogiLink®



## 48W Dual USB-C™ GaN Wall Charger

Art. No.: PA0231



### Compact size, Ultra-Powerful

Easy to carry with high output for laptops/ smartphones, simplify your luggage for traveling.



### Multiple Protection

Supports overcurrent, overvoltage, overheating and short circuit protection.

Best Connectivity



RoHS  
compliant



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.



PA0231



4 052792 057751

Made in China

# LogiLink®



## 48W Dual USB-C™ GaN Wall Charger

Art. No.: PA0231



### Wide Compatibility

Compatible with most mobile devices: smartphones, tablets, laptops and much more.

### Specification:

Input	100-240V AC 50/60Hz 1.5A
Output	USB-C 1: 5V 3A (15W) / 9V 2A (18W) max. USB-C 2: 5V 3A (15W) / 9V 3A (27W) / 15V 2A (30W) 20V 1.5A (30W) max. Max. total output: 48W
Protections	Overcurrent, overvoltage, overheating and short circuit
Operating Temperature	0~25°C
Storage Temperature	-20~85°C
Operating Relative Humidity	20%~90% (non-condensing)
Storage Relative Humidity	5%~95% (non-condensing)
Dimension	92 x 36 x 40mm
Weight	115g



PA0231



Made in China



RoHS  
compliant



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.


Best Connectivity

# LogiLink®



## 48W Dual USB-C™ GaN Wall Charger

Art. No.: PA0231



### Package Contents:

- » 1 x Dual USB-C GaN Wall Charger
- » 1 x User Manual

### Package Information:

- » Packing Dimension: mm
- » Packing Weight: kg
- » Carton Dimension: 0mm
- » Carton Q'ty: pcs
- » Carton Weight: kg



PA0231



4 052792 057751

Made in China



RoHS  
compliant



\*The specifications and pictures are subject to change without prior notice.  
\*All trade names referenced are the registered trademarks of their respective owners.

Best Connectivity