# SAUTER **CP 15-2Y1**

Single-point load cell made of anodised aluminium



## Category

| | |
|---|---|
| Brand | Sauter |
| Product categoriy | Measuring cell |
| Product group | Load cell |
| Product family | CP Y1 |

## Measuring System

| | |
|---|---|
| Weighing capacity [Max] | 15 kg |
| Load cell - characteristic value - nominal | 2 mV/V |
| Load cell - characteristic value - variance | 0,2 mV/V |
| Load cell OIML class | C2 |
| Load cell connection | 4-wire |
| Power supply + Colour | red |
| Power supply - Colour | black |
| Signal + Colour | green |
| Signal - Colour | white |
| Load cell - Dead load [Min] (%) | 0% |
| Measuring applications | mass |
| Directions of force | compression |
| Load sell - Input resistance - nominal | 405 Ω |
| Load cell - Input resistance - variance | 10 Ω |
| Load cell - Output resistance - nominal | 350 Ω |
| Load cell - Output resistance - variance | 3 Ω |
| Load cell - Recommended exitation voltage [Min] | 9 V |
| Load cell - Recommended exitation voltage [Max] | 12 V |
| Load cell - Isolation resistance - [Min] | 5000 MΩ |
| Load cell - Combined error | 0,03% |
| Zero balance | ≤± 1.5%FS |
| Safe overload | 120% |
| Ultimate overload | 150% |

## Functions

| | |
|---|---|
| IP protection - complete device | IP65 |

## Construction

| | |
|---|---|
| Material | aluminium |
| Design | Singlepoint load cell |
| Dimension (W×D×H) | 130×22×30 mm |
| Maximum platform size | 250×350 mm |
| Cable length | 0,45 m |
| Mounting - force application | 2 × threaded hole M6 |
| Mounting - force dissipation | 2 × threaded hole M6 |

## Environmental conditions

| | |
|---|---|
| Ambient temperature [Min] | -20 °C |
| Ambient temperature [Max] | 50 °C |
| Use temperature [Min] | -10 °C |
| Use temperature [Max] | 40 °C |
| Storage temperature [Min] | -30 °C |
| Storage temperature [Max] | 60 °C |

## Approval

| | |
|---|---|
| CE mark | ✓ |

## Product information

| | |
|---|---|
| GTIN/EAN number | 4045761246249 |
| REACH classification | no prohibited substances |

## Packing & Shipping

| | |
|---|---|
| Shipping method | Parcel service |
| Delivery time | 1 d |
| Dimensions packaging (W×D×H) | 170×110×25 mm |
| Net weight approx. | 0,10 kg |
| Gross weight approx. | 0,10 kg |
| Shipping weight | 0,1 kg |

# SAUTER **CP 15-2Y1**

Single-point load cell made of anodised aluminium

## Pictograms

### STANDARD




### OPTION

