




Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Cable Clamp Kit**

Cable Clamp Type: **Box and Lid**

Compatible With Connector Shell Size: **3**

Shielded: **No**

Cable Insulation Diameter Range: **9.91 mm [.39 in]**

Features

Product Type Features

Grommets	Without
Product Type	Accessory
D-Shaped Connector Accessories	Cable Clamp Kit

Body Features

Shield Plating Material	None
Cable Clamp Material	Polypropylene
Retainer Clip Material	Stainless Steel
Color	Black
Cable Clamp Type	Box and Lid
Cable Exit Angle	180° (In-Line), 90° (Right Angle)

Mechanical Attachment

Screw & Hole Thread Size	14702
--------------------------	-------

Dimensions

Cable Insulation Diameter Range	9.91 mm[.39 in]
---------------------------------	-----------------



Operation/Application

Compatible With Connector Shell Size	3
Shielded	No

Packaging Features

Packaging Quantity	1
Packaging Method	Kit

Other

Comment	All parts are packaged unassembled., Each kit is comprised of a cable clamp and male screw retainer hardware (2 each).
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-035-DCRSS203
D-Sub Crimp Recept Signal 25 Posn,
Socket Size 20, Shell Size 3

Also in the Series | **AMPLIMITE Kit**

D-Sub Backshells & Clamps(136)

D-Sub Contact Accessories(1)

D-Sub Covers(3)

D-Sub Locking & Mounting(122)

Customers Also Bought

TE Part #205210-8
D-Sub Crimp: Plug, Signal, 37 Posn,
Pin Size 20, Shell Size 4

TE Part #205209-7
D-Sub Crimp Recept Signal 37 Posn,
Socket Size 20, Shell Size 4

TE Part #1-499252-3
Bus Connector: Strain Relief, ATA

TE Part #1-5102156-1
AMP-LATCH UNIVERSAL HEADERS

TE Part #863024-1
LGH PLUG ASSY HV 7 PIN

TE Part #1-640518-0
03P MR II PLUG HSG V0 RED

TE Part #1-640519-0
04P MR II PLUG HSG V0 RED

TE Part #1-640521-0
09P MR II PLUG HSG V0 RED

TE Part #1-5207908-0
KIT S/R SCREW RET 90/180 DEG

TE Part #1734303-1
SHIELD FINGER 4025B-T



Documents

Product Drawings

STRAIN REL W/SCRW RET KIT,SZ 3

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_5207908-7_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_5207908-7_A.3d_igs.zip

English

Customer View Model

ENG_CVM_5207908-7_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Environmental Compliance

MD_5207908-7_07292013958_dmtec

English

MD_5207908-7_07292013958_dmtec

English