



Z-Type Marker

TE Internal #: EC0300-000
Z-Type Marker, Pre-Printed Markers, Push-On, 7 Marker Size,
Compatible Cable Diameter Range 2 – 3.2 mm [.08 – .13 in], Yellow,
Straight Cut
[View on TE.com >](#)

Identification & Labeling > Pre-Printed Markers



Marker Style: **Push-On**
Marker Size: **7**
Compatible Cable Diameter Range: **2 – 3.2 mm [.08 – .13 in]**
Primary Product Color: **Yellow**
Marker Cut: **Straight**

Features

Body Features

Marker Style	Push-On
Marker Size	7
Primary Product Color	Yellow
Primary Product Material	Flexible PVC

Dimensions

Compatible Cable Diameter Range	2 – 3.2 mm[.08 – .13 in]
Product Width	4.5 mm[.177 in]

Printer/Label Features

Marker Cut	Straight
Printed Marking	/

Packaging Features

Packaging Method	Reel
Packaging Quantity	1000

Other

Printed Marking Color	Black
-----------------------	-------

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 930554-000
[12510000](#)

Also in the Series | [Z-Type Marker](#)



Pre-Printed Markers(862)

Customers Also Bought



TE Part #829019-000
101A031-100/180-0



TE Part #E85726-000
TMS-SCE MILITARY GRADE SLEEVES



TE Part #EC0129-000
05803438



TE Part #EC0454-000
06153428



TE Part #EC0457-000
06153431

Documents

Product Drawings

05813438

English

Datasheets & Catalog Pages

Z-TYPE Marker Technical datasheet

English