EC1131-000 ✔ ACTIVE

Z-Type Marker

TE Internal #: EC1131-000

Z-Type Marker, Pre-Printed Markers, Push-On, 15 Marker Size, Compatible Cable Diameter Range 3.8 – 6.3 mm [.149 – .248 in], White, Straight Cut

View on TE.com >

Identification & Labeling > Pre-Printed Markers



Marker Style: **Push-On**

Marker Size: **15**

Compatible Cable Diameter Range: **3.8 – 6.3 mm [.149 – .248 in]**

Primary Product Color: **White**

Marker Cut: **Straight**

Features

Body Features

Marker Style	Push-On
Marker Size	15
Primary Product Color	White
Primary Product Material	Flexible PVC

Dimensions

Compatible Cable Diameter Range	3.8 – 6.3 mm[.149 – .248 in]
Product Width	4.5 mm[.177 in]

Printer/Label Features

Marker Cut	Straight
Printed Marking	6

Packaging Features

Packaging Quantity	1000

Other

Printed Marking Color	Black

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant

EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 008970-000
12550000

Also in the Series | Z-Type Marker



Pre-Printed Markers(862)

Customers Also Bought



TE Part #2-1879009-7
Wirewound Resistor: Horizontal Mount



TE Part #EC1044-000
Z-TYPE PUSH-ON MARKERS



TE Part #EC1126-000
06183901



TE Part #EC1128-000
06183903



TE Part #EC1127-000
06183902



TE Part #EC1125-000
06183900



TE Part #EC0703-000
06163919



TE Part #EC1129-000
06183904



TE Part #EC1156-000
06183931

Documents

Product Drawings

06183906

English

Datasheets & Catalog Pages

Z-TYPE Marker Technical datasheet

English

Product Specifications

RW-2535 Specification for Pre-Printed Markers

English