

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0334724801](#)
Status: **Active**
Overview: [MX150 Sealed and Unsealed Connector System](#)
Description: MX150 Mat-Sealed Female Connector Assembly, Dual Row, 8 Circuits, Keying Option A, without Connector Position Assurance, Black

Documents:

Drawing (PDF)	Application Specification AS-33472-100-CH-001 (PDF)
3D Model (PDF)	Application Specification AS-33611-001-001 (PDF)
3D Model	Packaging Specification PK-31300-903-001 (PDF)
Product Specification PS-33472-000-001 (PDF)	Datasheet (PDF)
Application Specification AS-33472-100-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	33472
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	889056886253

Physical

Circuits (maximum)	8
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	11.408/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-33472-100-001, AS-33472-100-CH-001, AS-33611-001-001
Packaging Specification	PK-31300-903-001
Product Specification	PS-33472-000-001
Sales Drawing	334720802-001, SD-33472-0001-001, SD-33472-0002-002



Series image - Reference only

**EU ELV
Compliant**

**EU RoHS
Compliant
REACH SVHC**

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

**Halogen-Free
Status**

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
33472 Series

Mates With

MX150 Male Sealed Connector [33482](#)

MX150 Male Bulkhead Twist-Lock
Sealed Connector [348404410](#)

Use With

MX150 Female Terminal [33012](#) , [33001](#)

MX150 Sealed Cavity Plug [343450001](#)

MX150 Backshell [349510811](#) ,
[349510821](#)