

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0334828601](#)
Status: **Active**
Overview: [MX150 Sealed and Unsealed Connector System](#)
Description: MX150 Mat-Sealed Male Connector Assembly, Dual Row, 16 Circuits, Keying Option A, without Connector Position Assurance, Black

Documents:

3D Model (PDF)	Packaging Specification PK-31300-635-001 (PDF)
3D Model	Packaging Specification PK-31300-903-001 (PDF)
Drawing (PDF)	Test Summary TS-33472-0001-001 (PDF)
Product Specification PS-33472-000-001 (PDF)	Datasheet (PDF)
Application Specification AS-33472-100-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-33472-100-CH-001 (PDF)	

General

Product Family	Crimp Housings
Series	33482
Application	Power, Wire-to-Wire
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	889056545273


Physical

Circuits (maximum)	16
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	18.111/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-33472-100-001, AS-33472-100-CH-001
Packaging Specification	PK-31300-635-001, PK-31300-903-001
Product Specification	PS-33472-000-001
Sales Drawing	334821602-001, SD-33482-0001-001, SD-33482-0002-001
Test Summary	TS-33472-0001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[33482](#) Series

Mates With

[33472](#) Female Dual Row Sealed Connector

Use With

[33000](#) MX150 Tin (Sn) Male Terminal,
[33011](#) Gold (Au) Male Terminal, [343450001](#)
MX150 Sealed Blade Cavity Plug