


PARAPROJECT®

Case TC20

Protect , TwinCharge , Transport



Part denomination	PARAPROJECT Case TC20 TwinCharge, incl. USB-A to Lightning® / LED cable, black
Part number	208721151
GTIN /EAN	4006793002937
Field of application	Education
Certificates	CE
Applicable standards	DIN EN 60950-1 / DIN EN 55022 / DIN EN 55024
Scope of delivery	<ul style="list-style-type: none"> - 1x Case TC20 with integrated TwinCharge technology - 1x device connecting cable, EU, length: 5m - 1x operating instruction for case and combination lock - 20x USB-A cables with Lightning connector and LED display with MFi certification, Boost Charge™ and nylon reinforcements, pre-installed
Materials	- X-ABS plastic
External dimensions (WxDxH)	720 mm x 390 mm x 550 mm
Weight	14450 g
Transport dimensions	760 mm x 420 mm x 570 mm
Dimensions of euro-pallets	1200 mm x 800 mm x 1860 mm
Number of euro-pallet	6
customs tariff number	85044082
Country of origin	RO
Fittings	<ul style="list-style-type: none"> - case lid: with various storage compartments and pockets for accessories and styluses - case body: TwinCharge charging unit with USB-C and A ports , 20 storage compartments for iPad - additionally: ventilation openings in the case lid and bottom for optimal air circulation - temperature sensor, main switch, overvoltage protection
Compatible devices	all iPad models up to 12.9“
Max. number of devices	20
Operating system	iOS
Power supply	4x TwinCharge modules for the complete power supply of devices
Output power per port	automatic adjustment via USB-PD Power Delivery and QuickCharge standards ; e.g. 20x iPad with 22W each per port, Boost Charge™ ; USB-C and USB-A output (22 / 30 / 45W): DC ; 5V/9V /12V/15V3A,20V2.25A
Optional accessories	<ul style="list-style-type: none"> - USB charging cable for USB-C to C, USB-C to Lightning, USB-A to Lightning - external week timer - USB data and charging cable with LED display for USB-C to Lightning, USB-A to Lightning
Lock types	combination lock
Connections	- - outside: central power supply with main switch and protective cap - inside: 20 x USB-A sockets each or USB-C socket, optional depending on cable type available

PARAPROJECT®

Case TC20

Protect , TwinCharge , Transport

Data of currents	- 100 - 240 V - max. 10 A - 50 / 60 Hz
Dimension of pockets	24 x 255 x 310 mm
Color	black

product image similar / information without content / subject to errors and changes / all dimensions in mm



- storage space for up to 20 tablets
- TwinCharge technology



- main switch
- overvoltage protection