

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0472861001](#)
Status: **Active**
Overview: [Battery Connectors](#)
Description: 2.00mm Pitch Battery Connector, Surface Mount, Contact Width 0.70mm, Dimple on Contact Area, Working Height 1.60mm, 4 Circuits, Lead-Free


Documents:	
3D Model	Product Specification PS-47286-001-001 (PDF)
Drawing (PDF)	Packaging Specification PK-47286-001-002 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	47286
Application	Board-to-Board, Signal
Comments	Dimple on Contact Area
Overview	Battery Connectors
Product Name	Battery Connector, Compression Connector, One Piece
UPC	822350798143

Physical	
Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Durability (mating cycles max)	10000
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	1.60mm
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.139/g
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.762µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Temperature Range - Operating	-20° to +70°C
Termination Interface: Style	Surface Mount

Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	200V

Solder Process Data	
Duration at Max. Process Temperature (seconds)	030
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	002



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[47286](#) Series

Process Temperature max. C	250
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-47286-001-002
Product Specification	PS-47286-001-001
Sales Drawing	SD-47286-001-001

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION