




Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: Locking Post Kit

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Locking Post Kit

Mechanical Attachment

Locking Post Plating Material	Zinc
Locking Post Finish	Yellow Chromate
Locking Post Material	Cold Rolled Steel
Screw & Hole Thread Size	4-40

Dimensions

Length	14.22 mm[.56 in]
--------	------------------

Operation/Application

For Use With	Cable Clamps
--------------	--------------

Packaging Features

Packaging Method	Kit
------------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions



China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.35% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 5206807-5 SLIDE LOCK POST,ZN PLTD	 TE Part # 5206514-9 SLIDING LOCK POST KIT
--	---

Also in the Series | **AMPLIMITE Kit**



D-Sub Backshells & Clamps(136)



D-Sub Contact Accessories(1)



D-Sub Covers(3)



D-Sub Locking & Mounting(122)

Customers Also Bought



TE Part #1658648-1
D-Sub Crimp: Plug, Signal, 25 Posn, Pin Size 20, Shell Size 3




TE Part #1-747944-5
IDC D-Sub: Connector Kit, Plug, Wire to Wire, Signal, 2.77 mm



TE Part #166054-1
D-Sub Connector Contacts: Pin, Brass, Signal, Size 20




TE Part #166052-1
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20



TE Part #160759-4
PL 250 TERMINAL REC 0.5-1.5 MM2 TPPHBZ



TE Part #1658687-1
D-Sub Crimp Recpt Signal 26 Posn, Socket Size 22, Shell Size 2



TE Part #2-640501-2
09P MR HDR ASSY VO RED LF



TE Part #ZPF000000000007441
983-0S 22-55 PN



TE Part #10202310-00
PRESS XDCR M5254-000004-05KPG



TE Part #20009558-00
PRESS XDCR M5254-000014-15KPG

Documents

Product Drawings
SLIDING LOCK POST KIT

English

CAD Files
3D PDF

English

Customer View Model
ENG_CVM_5206514-6_O.2d_dxf.zip



English

Customer View Model

[ENG_CVM_5206514-6_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_5206514-6_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_5206514-6_07172013328_dmtec](#)

English

[MD_5206514-6_07172013328_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English