



K-Type Marker

TE Internal #: EC6496-000

K-Type Marker, Pre-Printed Markers, Tie-On, 65 Marker Size,
Compatible Cable Diameter Range 4.2 – 7 mm [.165 – .276 in],
Yellow, Straight Cut

[View on TE.com >](#)

Identification & Labeling > Pre-Printed Markers



Marker Style: **Tie-On**
Marker Size: **65**
Compatible Cable Diameter Range: **4.2 – 7 mm [.165 – .276 in]**
Primary Product Color: **Yellow**
Marker Cut: **Straight**

Features

Body Features

Marker Style	Tie-On
Marker Size	65
Primary Product Color	Yellow
Primary Product Material	Flexible PVC

Dimensions

Compatible Cable Diameter Range	4.2 – 7 mm[.165 – .276 in]
Product Width	6 mm[.23 in]

Printer/Label Features

Marker Cut	Straight
------------	----------

Packaging Features

Packaging Quantity	500
--------------------	-----

Other

Printed Marking Color	Black
-----------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant









China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability









Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 4-160968-1 CABLE TY 134X2.6 NAT	 TE Part # 2-160975-1 CABLE TY 200X4.8 NAT	 TE Part # 4-160968-2 CABLE TY 134X2.6 BLACK	 TE Part # 4-160971-2 CABLE TY 140X3.6 BLACK
 TE Part # 4-160975-2 CABLE TY 200X4.8 BLA	 TE Part # 2-160982-1 CABLE TY 300X7.8 NAT	 TE Part # 2-160986-2 CABLE TY 750X7,8BLA	 TE Part # 2-100715-1 CABLE TY 150X3,6NAT



 TE Part # 2-100716-1 CABLE TY 200X4,8NAT	 TE Part # 2-160970-2 CABLE TY 200X2.6 BLA	 TE Part # 2-160978-1 CABLE TY 360X4,8NAT	 TE Part # 2-160983-2 CABLE TY 365X7.8 BLA
 TE Part # 4-160970-2 CABLE TY 200X2.6 BLA	 TE Part # 4-160975-1 CABLE TY 200X4.8 NAT	 TE Part # 4-160974-1 CABLE TY 178X4,8NAT	 TE Part # 2-160977-2 CABLE TY 290X4.8 BLA
 TE Part # 2-160978-2 CABLE TY 360X4,8BLA	 TE Part # 2-160968-1 FOAC CABLE TY NATURAL 134X2.6	 TE Part # 2-160981-2 CABLE TY 240X7.8 BLACK	 TE Part # 2-160968-2 CABLE TY 134X2.6 BLACK

Also in the Series | K-Type Marker



Pre-Printed Markers(93)

Customers Also Bought

 TE Part #557721-000 TMS-RJS-RIBBON-4RPSCE	 TE Part #EC6455-000 K-TYPE TIE-ON MARKERS	 TE Part #CU9289-000 Thick-Wall Heat Shrink Tubing	 TE Part #NB25882001 SCL-1/2-0-STK
--	---	--	--



TE Part #EC4942-000
11310000



TE Part #EC4943-000
11320000

Documents

Product Drawings

13611442

English

Datasheets & Catalog Pages

K-Type Markers

English

Product Specifications

RW-2535 Specification for Pre-Printed Markers

English