

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0002061132**
Status: **Active**
Overview: Standard .062"+ and Standard .062" Pin and Socket Connector Systems
Description: 1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1855, Female, with Tin (Sn) Plated Brass Contact, 24-30 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-1190-003-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	<u>1855</u>
Application	Power
Crimp Quality Equipment	Yes
Overview	<u>Standard .062"+ and Standard .062" Pin and Socket Connector Systems</u>
Packaging Alternative	<u>02061131 (Reel)</u>
Product Name	Standard .062"
UPC	800753616042

Physical


Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.130/g
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.02-2.29mm
Wire Size AWG	24, 26, 28, 30
Wire Size mm ²	N/A

Material Info

Engineering Number 1855-(P901)L

Reference - Drawing Numbers

Packaging Specification PK-1190-003-001
 Sales Drawing SD-1855-X-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

1855 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool for Standard .062" Diameter Male and Female Terminals	<u>11020001</u>
Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals	<u>11030002</u>
ServiceGrade Hand Crimp Tool for Field Repair Only, 14-24 AWG	<u>638111000</u>

PremiumGrade Hand638190800
Crimp Tool for Mini-
Fit Jr. Male and
Female Terminals,
22-28 AWG

This document was generated on 06/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION