

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008650114](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-002-001 \(PDF\)](#)
[Product Specification PS-08-50-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
Series [2478](#)
Application Power, Wire-to-Board
Crimp Quality Equipment Yes
Overview [KK Interconnect Solutions](#)
Packaging Alternative [08650115](#) (Loose)
Product Name KK 396, KK 508
UPC 800754227209

Physical

Gender Female
Material - Metal Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Gold
Net Weight 0.150/g
Packaging Type Reel
Plating min - Mating 0.381µm
Plating min - Termination 0.381µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 2.79mm max.
Wire Size AWG 18, 20, 22, 24
Wire Size mm² N/A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number 2478-3-(555)

Reference - Drawing Numbers

Packaging Specification PK-2759-002-001
Product Specification PS-08-50-001
Sales Drawing SD-2478-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[2478](#) Series

Use With

[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) ,
[5239](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description **Product #**

Extraction Tool [11030016](#)

for Flat Blade,
3.96mm KK,
2.00mm, 3.96mm
EdgeMate, and Ultra-
Fit Terminals

Terminator Die [11402096](#)

Hand Crimp Tool for [638279500](#)
3.96mm Pitch KK

Crimp Terminals,
18-24 AWG
Mini-Mac Applicator 638885000
for KK and Trifurcon,
3.96mm Terminals,
18-24 AWG, check
ATS for Wire
Insulation Diameter
Compatibility

This document was generated on 08/16/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION