

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0351500290](#)
Status: **Active**
Overview: [VersaBlade Wire-to-Wire Connector System](#)
Description: [VersaBlade Terminal Position Assurance \(TPA\) Retainer, 6.20mm Pitch, 2 Circuits, Natural](#)

Documents:

3D Model	Application Specification 351500000ASKOR-000 (PDF)
Drawing (PDF)	Packaging Specification PK-35150-002-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-35150-001-001 (PDF)	Brochure (PDF)
Product Specification PS-35150-003-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 351500000ASENG-000 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Accessories
Series	35150
Component Type	Terminal Position Assurance
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	800754375412

Physical

Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Natural
Flammability	94V-2
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.240/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +120°C

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Packaging Specification	PK-35150-002-001
Product Specification	PS-35150-001-001, PS-35150-003-001
Sales Drawing	SD-35150-029X



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[35150](#) Series

Use With

VersaBlade Standard Receptacle Housings
[351500200](#) , [351500204](#) , [351500209](#)
 , [351503209](#) , [351500210](#) , [351500214](#)
 , [351500219](#) , [351503219](#) , [351504209](#)
 , [351504219](#) , [351500400](#) , [351500404](#)
 , [351500409](#) , [351500410](#) , [351500412](#)
 , [351500414](#) , [351500419](#) , [351504419](#)

 VersaBlade Standard Plug Housings
[351510210](#) , [351510214](#) , [351510219](#) ,
[351512219](#) , [351513219](#) , [351514219](#)
 , [351510410](#) , [351510414](#) , [351510419](#)
 , [351514419](#)
 VersaBlade Multi-
Module 2-3-4 Receptacle Housings [35524](#) ,
[2026500909](#)