

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0428171044

Status:

Active

Overview:

Mini-Fit Sr. Power Connectors

Description:

Mini-Fit Sr. Crimp Terminal, Male, 14-16 AWG, Silver (Ag)

Documents:

Drawing (PDF)

Product Specification PS-42815-001-001 (PDF)


Application Specification AS-42815-001-001 (PDF)

Packaging Specification PK-42815-001-001 (PDF)

Test Summary TS-42815-004-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	42817
Application	Power, Wire-to-Wire
Comments	High Current/Low Force See Product Specification for maximum current rating by circuit size and application.
Crimp Quality Equipment	Yes
Overview	Mini-Fit Sr. Power Connectors
Product Name	Mini-Fit Sr.
UPC	889056244770
Physical	
Gender	Male
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Silver
Material - Plating Termination	Tin
Net Weight	1.376/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.57mm max.
Wire Size AWG	14, 16
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	50.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-42815-001-001
Application Tooling Documents	ATS-638912000-001
Packaging Specification	PK-42815-001-001
Product Specification	PS-42815-001-001
Sales Drawing	SD-42817-020-001
Test Summary	TS-42815-004-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2020)9139-DC (19

Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

42817 Series

Use With

Mini-Fit Sr. Plug Housings 42818 , 43938

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

PremiumGrade

638113800

Hand Crimp Tool for 10.00mm Mini-Fit Sr. Male and Female Terminals, 14-16 AWG

Extraction Tool for Mini-Fit Sr. Terminals, 8-16 AWG

638130400

Mini-Mac Applicator 638912000
for Mini-Fit Sr.
Male and Female
Terminals for 14-16
AWG Wire with
Insulation Diameter
no greater than
3.33mm

This document was generated on 08/18/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION