

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0436400801

Status:

Active

Overview:

Micro-Fit Connector System

Description:

Micro-Fit 3.0 Plug Housing, Single Row, 8 Circuits, UL 94V-0, Low-Halogen, Black

- Documents:
- 3D Model

Test Summary 430450005-TS-000 (PDF)
- Drawing (PDF)

Test Summary TS-43045-001-001 (PDF)
- 3D Model (PDF)

Test Summary TS-43045-002-001 (PDF)
- Product Specification 436500001-PS-JA-000 (PDF)

Test Summary TS-43045-003-001 (PDF)
- Product Specification 436500001-PS-KO-000 (PDF)

Test Summary TS-46235-001-001 (PDF)
- Product Specification 436500001-PS-SP-000 (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-43650-001 (PDF)

Product Literature (PDF)
- Packaging Specification PK-43640-003-001 (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	43640
Application	Power, Wire-to-Wire
Overview	Micro-Fit Connector System
Product Name	Micro-Fit 3.0
UPC	800754712538
Physical	
Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.330/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Solder Process Data	
Lead-freeProcess Capability	N/A

Material Info

Reference - Drawing Numbers	
Packaging Specification	PK-43640-003-001
Product Specification	436500001-PS-JA-000, 436500001-PS-KO-000, 436500001-PS-SP-000, PS-43650-001
Sales Drawing	SD-43640-XXXX-001
Test Summary	430450005-TS-000, TS-43045-001-001, TS-43045-002-001, TS-43045-003-001, TS-46235-001-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

43640 Series

Mates With

Micro-Fit 3.0 Receptacle Housing 43645

 Micro-Fit 3.0 Cable Assembly 214750 , 214751

Use With

Micro-Fit 3.0 Crimp Terminals 43031
 Micro-Fit 3.0 Pre-Crimped Lead 214762 , 214763

This document was generated on 08/24/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION