

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0522713069

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Bottom Contact, 3.00mm Height, 30 Circuits, Gold Plating



Series image - Reference only

Documents:

- [3D Model \(PDF\)](#)[Packaging Specification SPK-52271-002-001 \(PDF\)](#)
- [3D Model](#)[Datasheet \(PDF\)](#)
- [Drawing \(PDF\)](#)[Product Guide \(PDF\)](#)
- [Product Specification PS-52271-054-001 \(PDF\)](#)[RoHS Certificate of Compliance \(PDF\)](#)
- [Application Specification AS-52271-001-001 \(PDF\)](#)[Reference Guide \(PDF\)](#)

Agency Certification

CSA

LR19980

General

Product Family

Series

Overview

Product Name

Series Name

UPC

FFC/FPC Connectors

52271

Easy-On FFC FPC Connectors

Easy-On

Slider

822350052658

Physical

Actuator Type

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Contact Position

Durability (mating cycles max)

Flammability

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Mounting

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to PCB

Stackable

Temperature Range - Operating

Wire/Cable Type

Slider

30

30

Natural

Bottom

30

94V-0

3.00mm

Phosphor Bronze

Gold

Tin

Nylon

1370.250/mg

1

Right Angle

No

Surface Mount

Yes

Embossed Tape on Reel

1.00mm

1.00mm

Yes

No

-40° to +85°C

FFC/FPC

Electrical

Current - Maximum per Contact

Voltage - Maximum

0.5A

50V

Material Info

Reference - Drawing Numbers

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

52271 Series

Mates With

Premo-Flex FFC Cable [15039](#)

Application Specification
Packaging Specification
Product Specification
Sales Drawing

AS-52271-001-001
SPK-52271-002-001
PS-52271-054-001
SD-52271-038-001, SD-52271-039-001

This document was generated on 08/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION