

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0541325062

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Bottom Contact, 2.00mm Height, 50 Circuits, Gold Plating

Documents:

- [Drawing \(PDF\)](#)

[3D Model](#)

[3D Model \(PDF\)](#)

[Product Specification PS-54132-061-001 \(PDF\)](#)

[Packaging Specification SPK-54132-001-001 \(PDF\)](#)
- [Datasheet \(PDF\)](#)

[Product Guide \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Reference Guide \(PDF\)](#)

Agency Certification

UL

E29179

General

Product Family

Series

Overview

Product Name

Series Name

UPC

FFC/FPC Connectors

54132

Easy-On FFC FPC Connectors

Easy-On

Slider

822348709014

Physical

Actuator Type

Circuits (Loaded)

Color - Resin

Contact Position

Durability (mating cycles max)

Flammability

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Mounting

PCB Retention

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Wire/Cable Type

Slider

50

Black, Natural

Bottom

20

94V-0

2.00mm

Phosphor Bronze

Gold

Gold

High Temperature Thermoplastic

544.000/mg

1

Right Angle

No

Surface Mount

Yes

Embossed Tape on Reel

0.50mm

0.102µm

0.051µm

Yes

No

N/A

-20° to +85°C

FFC/FPC

Electrical


Current - Maximum per Contact

Voltage - Maximum

0.5A

50V

Material Info



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

54132 Series

Mates With

Premo-Flex FFC Cable [15020](#)

Reference - Drawing Numbers

Packaging Specification	SPK-54132-001-001
Product Specification	PS-54132-061-001
Sales Drawing	SD-54132-064-001, SD-54132-065-001, SD-54132-065-002

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION