

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **5600850101**  
**Status:** **Active**  
**Overview:** DuraClik Connector System  
**Description:** DuraClik Crimp Terminal, Female, 22-26 AWG, Reel

**Documents:**

Drawing (PDF) Packaging Specification PK-560085-001-001 (PDF)  
Product Specification PS-502351-001-001 (PDF) RoHS Certificate of Compliance (PDF)  
Application Specification AS-560085-001-JP-001 (PDF)



Series image - Reference only

**General**

Product Family Crimp Terminals  
Series 560085  
Application Automotive, Power, Signal, Wire-to-Board  
Crimp Quality Equipment Yes  
Overview DuraClik Connector System  
Product Name DuraClik  
UPC 887191151892

**Physical**

Gender Female  
Material - Metal Phosphor Bronze  
Material - Plating Mating Tin  
Material - Plating Termination Tin  
Net Weight 0.024/g  
Packaging Type Reel  
Termination Interface: Style Crimp or Compression  
Wire Insulation Diameter 1.40mm  
Wire Size AWG 22, 24, 26  
Wire Size mm<sup>2</sup> 0.34

**Electrical**

Voltage - Maximum 125V

**Solder Process Data**

Lead-freeProcess Capability N/A

**Material Info**

**Reference - Drawing Numbers**

Application Specification AS-560085-001-JP-001  
Application Tooling Documents 571753710ATS-000, 571753710ATS-J-000  
Packaging Specification PK-560085-001-001  
Product Specification PS-502351-001-001  
Sales Drawing SD-560085-001-001

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

560085 Series

**Use With**

502351 DuraClik Wire-to-Board Receptacle Housing

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool for 11030043  
Micro-Fit Terminals  
FineAdjust Applicator 2037021900  
for 2.0 Wire-to-Board  
Crimp Receptacle  
Terminal and SMEC  
Crimp Receptacle  
Terminals, 22-26  
AWG and AVSS 0.3  
Wires

PremiumGrade Hand638235100  
Crimp Tool for Micro-  
Latch, DuraClik, and  
Servo Motor Encoder  
Female Terminals,  
22-26 AWG

This document was generated on 08/17/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**