

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0638132300](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Extraction Tool for 1.50mm CP Crimp Terminals for CMC Connector

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	207121
Comments	<p style="margin-top: 0; margin-bottom: 0">See Tooling Specification (PDF) Above</li><li><p style="margin-top: 0; margin-bottom: 0">Extraction Tool for removal of 98915 Series</li>
Function	Extraction
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	N/A
Tool Type	Extraction Hand Tool
UPC	800756711881
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.


**Physical**

Net Weight 4.950/zg

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents  
ATS-638132300-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

207121 Series

**Application Tooling Description**

**FAQ Product #**

1.50mm CMC CP Female Terminal, Tin Plated, for Tab Dimensions 1.50mm x 0.80mm, Wire Size 0.50mm<sup>2</sup> - 1.0mm<sup>2</sup> [643231029](#)

1.50mm CMC CP Female Terminal, Tin plated, for Tab Dimensions 1.50mm x 0.80mm, Wire Size > 1.0mm<sup>2</sup>- 2.0mm<sup>2</sup>

[643231039](#)

1.50mm CMC CP Female Terminal, Tin plated; Selective 1.27µm Gold in Contact Area, for Tab Dimensions 1.5mm x 0.8mm, Wire Size > 1.0mm<sup>2</sup> -2.0mm<sup>2</sup>

[643231219](#)

1.50mm CMC CP 643231319  
Female Terminal,  
Tin plated; Selective  
1.27 $\mu$ m Gold in  
Contact Area, for  
Tab Dimensions  
1.5mm x 0.8mm,  
Wire Size 0.5mm<sup>2</sup>  
-1.0mm<sup>2</sup>

This document was generated on 07/27/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**