

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0734036282](#)  
**Status:** **Active**  
**Overview:** [FAKRA PCB, Cable and Sealed Connection Systems](#)  
**Description:** 50 Ohms, FAKRA SMB Jack, Straight, for RG-316 / RG-174 Cable, Keying Code C, Blue

**Documents:**

[3D Model](#) [Application Specification AS-73597-046-001 \(PDF\)](#)  
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**General**

|                 |  |
|-----------------|--|
| Product Family  | RF/Coax Connectors   |
| Series          | <a href="#">73403</a>  |
| Application     | Automotive   |
| Overview        | <a href="#">FAKRA PCB, Cable and Sealed Connection Systems</a> |
| Product Name    | FAKRA, SMB   |
| Style           | Cable  |
| Type            | Subminiature   |
| UPC             | 887191449609   |
| Wire/Cable Type | RG-174, RG-316   |

**Physical**

|                       |          |
|-----------------------|----------|
| Gender                | Jack     |
| Keying to Mating Part | Yes      |
| Net Weight            | 3.021/g  |
| Orientation           | Straight |
| PCB Mounting          | N/A      |
| Packaging Type        | Bag      |
| Panel Mount           | No       |
| Panel Mount Method    | N/A      |
| Reverse Polar         | No       |

**Electrical**

|                 |                             |
|-----------------|-----------------------------|
| Frequency       | 6 GHz                       |
| Impedance       | 50Ω                         |
| Power / Voltage | VOLTAGE: 335 Vrms@Sea Level |


**Solder Process Data**

|                             |     |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

**Material Info**

**Reference - Drawing Numbers**

|                           |                  |
|---------------------------|------------------|
| Application Specification | AS-73597-046-001 |
| Sales Drawing             | SD-73403-628     |



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

Lead

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Relevant

**Search Parts in this Series**

[73403 Series](#)