

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0901192121](#)
Status: **Active**
Overview: [C-Grid III Interconnects](#)
Description: C-Grid III Crimp Terminal, 26-28 AWG, Bag, 0.38µm Selective Gold (Au)

Documents:

| | |
|---|--|
| 3D Model | Application Specification 901190001-AS-000 (PDF) |
| 3D Model (PDF) | Packaging Specification PK-90119-101-001 (PDF) |
| Drawing (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-99020-0001-001 (PDF) | |

General

| | |
|-------------------------|--|
| Product Family | Crimp Terminals |
| Series | 90119 |
| Application | Signal, Wire-to-Board |
| Comments | Loose Piece |
| Crimp Quality Equipment | Yes |
| Overview | C-Grid III Interconnects |
| Packaging Alternative | 901190121 (Reel) |
| Product Name | C-Grid III |
| UPC | 800753721418 |

Physical

| | |
|--------------------------------|----------------------|
| Gender | Female |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Net Weight | 0.073/g |
| Packaging Type | Bag |
| Plating min - Mating | 0.381µm |
| Plating min - Termination | 3.048µm |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 0.76-1.22mm |
| Wire Size AWG | 26, 28 |
| Wire Size mm ² | N/A |


Solder Process Data

| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|-------------------|
| Application Specification | 901190001-AS-000 |
| Crimp Specification | CS-90119-0111-002 |
| Packaging Specification | PK-90119-101-001 |
| Product Specification | PS-99020-0001-001 |
| Sales Drawing | SD-90119-001 |



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[90119 Series](#)

Use With

C-Grid III Modular Crimp Housing [90156](#) ,
[90123](#) , [90142](#) , [90143](#) , [90160](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

| | |
|---|---------------------------|
| Hand Crimp Tool For | 638258200 |
| C-Grid III Female Crimp Terminals, 26-28AWG | |
| Extraction Tool for C- | 690080003 |
| Grid III Terminals | |
| Insertion Tool for C- | 690080140 |
| Grid III Pre-crimped Terminals | |

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION