


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0901471103](#)
Status: **Active**
Overview: [C-Grid Connector Products](#)
Description: C-Grid PC Board Connector, Single Row, Vertical, 3 Circuits, Tin (Sn) Plating



Documents:
[3D Model](#) [Application Specification 713080001-AS-000 \(PDF\)](#)
[3D Model \(PDF\)](#) [Application Specification 901190001-AS-000 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-99020-0001-001 \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179

General
Product Family PCB Receptacles
Series [90147](#)
Application Board-to-Board, Signal
Overview [C-Grid Connector Products](#)
Product Name C-Grid
UPC 800753676886

Physical
Circuits (Loaded) 3
Circuits (maximum) 3
Color - Resin Black
Flammability 94V-0
Glow-Wire Capable No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part No
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Polyester
Net Weight 1.206/g
Number of Rows 1
Orientation Vertical
PC Tail Length 2.90mm
PCB Locator No
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tube
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Plating min - Mating 1.016µm
Plating min - Termination 1.016µm
Polarized to PCB No
Surface Mount Compatible (SMC) N/A
Temperature Range - Operating -55° to +105°C
Termination Interface: Style Through Hole

Electrical
Current - Maximum per Contact 3.0A
Grounding to PCB No
Voltage - Maximum 350V

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2020)9139-DC (19
Jan 2021)
Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[90147 Series](#)

Mates With
[90120](#) , [90121](#)

Use With
[90120](#) , [90121](#)

Solder Process Data

Lead-freeProcess CapabilityWAVE

Material Info

Reference - Drawing Numbers

Application Specification713080001-AS-000, 901190001-AS-000
Product SpecificationPS-99020-0001-001
Sales DrawingSDA-90147-001

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION