

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0923150815**

Status: **Active**

Overview: Picoflex Ribbon-Cable Connectors

Description: Picoflex PF-50 IDT-to-Picoflex PF-50 IDT Cable Assembly, 0.15m Length, Tin (Sn) Plating, 8 Circuits

Documents:

3D Model Product Specification PS-99020-0011-001 (PDF)

Drawing (PDF) RoHS Certificate of Compliance (PDF)

Application tooling part link

Application Tooling Part Link 62100-6000

Application Tooling Part Link 62100-6010

General

Product Family Cable Assemblies

Series 92315

Assembly Configuration Dual Ended Connectors

Connector to Connector Picoflex IDT-to-IDT

Overview Picoflex Ribbon-Cable Connectors

Product Name Picoflex

UPC 800754018593

Physical

Cable Length 0.15m

Circuits (Loaded) 8

Color - Resin Natural

Gender Female-Female

Lock to Mating Part None

Material - Metal Phosphor Bronze

Material - Plating Mating Tin

Material - Plating Termination Tin

Material - Resin Polyester

Net Weight 3.060/g

Number of Rows 2

Packaging Type Bag

Pitch - Mating Interface 1.27mm

Plating min - Mating 2.032µm

Plating min - Termination 2.032µm

Single Ended No

Termination Interface: Style IDT or Pierce

Waterproof / Dustproof No

Wire Insulation Diameter N/A

Wire Size AWG 28

Wire/Cable Type PVC, Ribbon Cable

Electrical

Current - Maximum per Contact 1.2A

Shielded No


Voltage - Maximum 250V

Material Info

Reference - Drawing Numbers

Product Specification PS-99020-0011-001

Sales Drawing SD-92315-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

92315 Series

Mates With

Picoflex PF-50 Header 90325 , 90800 ,
90779 , 90715 , 90814

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extractor Tool for 621006000
Connectors

This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION