



MEET LIKE YOU MEAN IT

BENEFITS

- Always look professional with exceptional camera optics that are optimized for video conferencing
- Make sure you're heard clearly with a built-in directional microphone that focuses on your voice, not the noise around you
- Enhance security and privacy, and ensure you are in control of when you are on camera with the integrated privacy shutter
- Poly Lens cloud management gives IT powerful tools to manage and track devices from anywhere

POLY STUDIO P5

The Poly Studio P5 webcam ensures you look your best on video calls at home, in the office, or wherever you're working. Exceptional camera optics are fine-tuned so you always come across clearly with a professional-quality image. Brilliant colors and automatic low light compensation deliver excellent video quality no matter where you need to take a call. The directional microphone focuses on your voice and not the noise around you. An integrated privacy shutter keeps you in control of when you are on camera for enhanced security and privacy. For IT, Poly Lens cloud management provides robust tools to manage and track devices from anywhere.

- Exceptional camera optics
- Automatic low-light compensation
- Built-in directional microphone
- Integrated privacy shutter
- USB connection to wireless headset adapter

POLY STUDIO P5



SPECIFICATIONS

CAMERA

- 1080p (Full HD), 720P (HD) Compatible
- Auto focus with 4x zoom / EPTZ
- 80° DFOV
- Low light quality & true color images
- Custom controls through Poly Lens Desktop

MICROPHONE

- Single directional microphone optimized for personal workspaces
- 50 Hz to 16 kHz frequency response

SYSTEM REQUIREMENTS

- Windows version 8.1, 10
- Mac OS X version 10.7 or later
- USB 2.0 port

DEVICE DRIVER SUPPORT

- USB 2.0
- UVC/UAC Plug and Play compatible

COMPATIBILITY

- Compatible with any application that supports standard USB/UVC standards

MANAGEABILITY

- Cloud: Poly Lens service
- Local (Windows/Mac): Poly Lens Desktop App

OTHER FEATURES

- Integrated USB 2.0 Type A cable
- Integrated privacy shutter
- Adjustable monitor clamp
- Tripod ready
- USB-A port built-in for wireless headset adapter
- Status LED indicates calling and mute state

DIMENSIONS

Camera body only:

- 1.5 W x 1.3 H x 2.4 D (Inches)
- 37.7 W x 34 H x 62 D (MM)

Camera with monitor clamp:

- 2.4 D x 1.7 H x 2.7 D (Inches)
- 60 W x 43 H x 68 D (MM)

OPERATING CONDITIONS

- Temperature: 0° C to +40° C
- 5% to 95% relative humidity, non-condensing
- Altitude: Up to 10,000 ft

PACKAGE CONTENTS

- Poly Studio P5 webcam
- Removable monitor clamp
- Setup sheet

LEARN MORE

For more information on the Poly Studio P5 webcam, please visit www.poly.com/studio-p5

PLANTRONICS + POLYCOM =  poly