




Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Cable Clamp Kit**

Cable Clamp Type: **Clam Shell**

Compatible With Connector Shell Size: **4**

Shielded: **No**

Cable Insulation Diameter Range: **12.45 mm [.49 in]**

Features

Product Type Features

Clam Shell Length	Standard
Grommets	Without
Product Type	Accessory
D-Shaped Connector Accessories	Cable Clamp Kit

Body Features

Shield Plating Material	None
Cable Clamp Material	Thermoplastic
Retainer Clip Material	Stainless Steel
Cable Clamp Type	Clam Shell
Cable Exit Angle	180°, 45°

Mechanical Attachment

Screw & Hole Thread Size	14702
--------------------------	-------

Dimensions

Cable Insulation Diameter Range	12.45 mm[.49 in]
---------------------------------	------------------

Operation/Application

Compatible With Connector Shell Size	4
Shielded	No

Packaging Features

--	--



Packaging Quantity	1
Packaging Method	Bag

Other

Comment	Each kit is comprised of a cable clamp and male screw retainer hardware (2 each).
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (.35% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 5205731-1
CLAMSHELL ASSEMBLY




TE Part # 5205979-1
FILLISTER HEAD SCREW,ZN



TE Part # 205723-1
CABLE CLAMP HSG

Also in the Series | **AMPLIMITE Kit**



D-Sub Backshells & Clamps(135)



D-Sub Contact Accessories(1)



D-Sub Covers(3)



D-Sub Locking & Mounting(120)

Customers Also Bought




TE Part #796692-5
TERMI-BLOK PCB MOUNT 1&2 5P.5




TE Part #5745175-2
CABLE CLAMP KIT,SZ 5



TE Part #3-747579-4
SHLDNG FERRULE, PLTD, BULK PKG



TE Part #5206478-1
CLAMSHELL KIT W/RETAINER,SZ 1



TE Part #5206478-2
CLAMSHELL KIT W/RETAINER,SZ 2



TE Part #1318697-6
Contact: Component To Wire ; 20-45A • 20-8 wire size



TE Part #2345832-2
REC. KIT (CONT. ADD.) NEW MOTO. PF



TE Part #5745175-4
CABLE CLAMP KIT,SZ 5



TE Part #1-5173856-1
070 MLC CAP ASSY 8P



Documents

Product Drawings

CLAMSHELL SIZE 4

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5206478-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5206478-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5206478-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Environmental Compliance

TE Material Declaration

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English