



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Locking & Mounting



D-Shaped Connector Accessories: **Screw Retainer Kit**

Screw Length: **7.62 mm [.3 in]**

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Screw Retainer Kit

Mechanical Attachment

Screw Plating Material	Zinc
Screw Material	Steel
Screw Finish	Clear Chromate
Screw & Hole Thread Size	4-40
Screw Length	7.62 mm[.3 in]

Operation/Application

For Use With	Metal Shell and All Plastic Connectors (HDF)
--------------	--

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag, Bulk

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (.35% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5745189-1
37 RCPT SP/MS STD



TE Part # 5745136-4
MALE SCRW RETAINER KT,BULK PKG

Also in the Series | **AMPLIMITE HDF**



D-Sub Locking & Mounting(8)



IDC D-Sub Connectors(36)

Customers Also Bought



TE Part #1-794611-2
MICRO MNL RPT CNT,LS PC,30AU L



TE Part #350570-7
UMNL SOK 24-18 AUBR




TE Part #1-794613-0
PIN CONT 26-30 TIN PLATE L/P




TE Part #50839-1
PIDG PTFE STRATO RING 14 6



TE Part #860267-1
LGH-6 PIN HV PLUG ASY




TE Part #4-2176348-2
CRGCQ 2010 6M8 5%



TE Part #5554726-1
SCREW,PAN HD, CPTV,SHLD CHAMP



TE Part #2063384-1
SDE FASTON 250 1.0-2.5mm2 ASSY



TE Part #CJ6400-000
202K153-25/225-CS-2065-0

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5746881-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5746881-2_A.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_5746881-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English